



00-07-17

PRODUKTINFORMATION

Vi reserverar oss mot fel samt förbehåller oss rätten till ändringar utan föregående meddelande

ELFA artikelnr

73-250-61 78250 trafo till MAX250


features

- Maxim Compatible
- Isolation to 4kV
- Surface Mount Options
- Toroidal Construction
- Standard Pinout
- UL 94V-0 Package Material
- Fully Encapsulated
- Low Profile
- Industrial Temperature Range

description


The 78250 series of converter transformers are specifically designed for use with Maxim chipsets to provide isolated RS232 interfaces. Carefully controlled turns ratios ensure consistent performance whilst a toroidal construction minimises EMI.

The surface mount devices are fully compatible with CECC00802 to 280°C which allows them to be placed and reflowed with IC's thus reducing time and cost in production.




pin connections

6 Pin DIP (top view)



6 Pin SM (top view)*



*Pin 5 is connected to secondary centre tap.

PRELIMINARY

Notice : This is not a final specification.
Some parametric limits may be subject to change.

78250

Converter Transformer

absolute maximum ratings

Operating free air temperature range ······ –40°C to 85°C

Storage temperature range ······ –50°C to 125°C

Lead Temperature 1.5mm from case for 10 seconds ······ 300°C

Peak current I_{PK} ······ 300mA

Isolation voltage 78250(M) (flash tested for 1 second) ······ 1500Vrms

Isolation voltage 78250V(M) (flash tested for 1 second) ······ 4000Vrms

electrical specifications over operating free air temperature range¹

78250

Parameter	Conditions	MIN	NOM	MAX	Package Style	Units
Primary Inductance, L_p	10kHz, 100mV	1.0	2.0	2.5	1	mH
Leakage Inductance, L_L	100kHz, 100mV		2.0	3.0		μ H
Interwinding Capacitance, C_{WW}	100kHz, 100mV		69	90		pF
D.C. Resistance, R_{DC}	<0.1VDC		1.0	2.0		Ω
Volt-time Product, E_T	5kHz, 5V	50				V μ s

electrical specifications over operating free air temperature range¹

78250M

Parameter	Conditions	MIN	NOM	MAX	Package Style	Units
Primary Inductance, L_p	10kHz, 100mV	1.0	2.0	2.5	2	mH
Leakage Inductance, L_L	100kHz, 100mV		2.0	3.0		μ H
Interwinding Capacitance, C_{WW}	100kHz, 100mV		69	90		pF
D.C. Resistance, R_{DC}	<0.1VDC		1.0	2.0		Ω
Volt-time Product, E_T	5kHz, 5V	50				V μ s

¹ All data taken at $T_A=25^\circ\text{C}$.

electrical specifications over operating free air temperature range¹

78250V

Parameter	Conditions	MIN	NOM	MAX	Package Style	Units
Primary Inductance, L_p	10kHz, 100mV	1.0	2.0	2.5	1	mH
Leakage Inductance, L_L	100kHz, 100mV		35	40		μ H
Interwinding Capacitance, C_{WW}	100kHz, 100mV		9	12		pF
D.C. Resistance, R_{DC}	<0.1VDC		1.4	1.8		Ω
Volt-time Product, E_T	5kHz, 5V	50				V μ s

electrical specifications over operating free air temperature range¹

78250MV

Parameter	Conditions	MIN	NOM	MAX	Package Style	Units
Primary Inductance, L_p	10kHz, 100mV	1.0	2.0	2.5	2	mH
Leakage Inductance, L_L	100kHz, 100mV		35	40		μ H
Interwinding Capacitance, C_{WW}	100kHz, 100mV		9	12		pF
D.C. Resistance, R_{DC}	<0.1VDC		1.4	1.8		Ω
Volt-time Product, E_T	5kHz, 5V	50				V μ s


¹ All data taken at $T_A=25^\circ\text{C}$.

78250

Converter Transformer

typical characteristics


Isolated RS-232 interface




OPTO'S - 4 x 4N26 (78250(M)), 4 x CNY17-3 (78250V(M))

outline dimensions¹

6 Pin DIP package style



recommended footprint details




¹ All dimensions in mm XX.XX ± 0.25mm.
All pins on a 2.54mm pitch and within ±0.25mm of true position.

78250


Converter Transformer

outline dimensions¹

6 Pin SM package style



recommended footprint details



¹ All dimensions in mm XX.XX ± 0.25mm.
All pins on a 2.54mm pitch and within ±0.25mm of true position.

INFORMATION

The following Newport Components publications are also available :

- The Power Components Handbook (also in CD ROM format)
- EMC Design Guidelines

Please contact Newport Components or your local supplier for a copy of these data books.



FM 13273 / RS 31306

Newport Components Limited reserve the right to alter or improve the specification, internal design or manufacturing process at any time, without notice. Please check with your supplier or visit our web site to ensure that you have the current and complete specification for your product before use.

For information and instructions on use, please consult the current Power Handbook.

© Newport Components Limited 2000

No part of this publication may be copied, transmitted or stored in a retrieval system or reproduced in any way including, but not limited to, photography, photocopy, magnetic or other recording means, without prior written permission from Newport Components Limited.

Newport Components Limited

1 Tanners Drive, Blakelands North
Milton Keynes MK14 5BU, England

Tel: +44 (0)1908 615232
Fax: +44 (0)1908 617545
email: info@newport-comps.com
www: <http://www.newport-comps.com>

MEMBERS OF NEWPORT TECHNOLOGY GROUP

Newport Components Inc.

8917 Glenwood Avenue, Raleigh
NC 27612, USA

Tel: +1 (919) 571-9405
Fax: +1 (919) 571-9262
email: info@us.newport-comps.com



9000SA078250 Issue 3 03/00 DCR 2527