

JALAS® 1335 BLACK

EN ISO 20345:2011, S3 SRB HRO CI

PROPERTIES

Highest level of protection, excellent grip, perfect fit, extra comfortable, excellent shock absorption

SPECIFICATION

TYPE OF SHOE Safety footwear, low shoes

NAIL PROTECTION MATERIAL Plasma-treated composite (PTC) textile

FITTING Regular

SIZE RANGE 36-47

COLLECTION Grip

PLATFORM Grip

UPPER MATERIAL Full-grain leather

UPPER MATERIAL THICKNESS 1,6-1,8

TOECAP MATERIAL Aluminium

LINING MATERIAL Polyester, polyamide

SOLE MATERIAL PU midsole, plastic shank, rubber outsole

INSOLE FX2 Pro

INSOLE MATERIAL Textile, soft EVA, polyester-based conductive thread, double shock absorption zones in Poron® XRD®

FASTENING Laces

COLOUR Black



SIZE	ART. NO.	EAN NO.
36	1335-36	6408487420054
37	1335-37	6408487420061
38	1335-38	6408487420078
39	1335-39	6408487420085
40	1335-40	6408487420092
41	1335-41	6408487420108
42	1335-42	6408487420115
43	1335-43	6408487420122
44	1335-44	6408487420139
45	1335-45	6408487420146
46	1335-46	6408487420153
47	1335-47	6408487420160

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

JALAS® 1335 BLACK

FEATURES

Heat-resistant outsole, oil-resistant outsole, anti-static properties, polstered shaft edge, ventilating insole, water repellent, double shock absorption zones, conforms with IEC 61340-5-1 (ESD)

PRIMARY PROTECTION

Prevents risk of: toe injuries, nail penetration, antistatic

PRIMARY ENVIRONMENTS OF USE

Outdoors, environments with risk for outsole penetration



CE



Aluminium toecap



ESD



Nail protection in plasma-treated composite (PTC) textile



Heat-resistant outsole



Water repellent



Oil-resistant outsole



Ergo-Shock Absorption System



Anti-static properties

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2015-09-29

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com

JALAS® 1335 BLACK

COMPLIANCE
EN ISO 20345:2011

COMPLIANCE DESCRIPTION

SB: Footwear with toe protection tested with 200 J impact and 15kN compression force (includes oil resistant outsole)

S1: Footwear made from leather and other materials excluding all-rubber or all-polymeric footwear + closed seat region + SB + A + E

S2: S1 + WRU

S3: S2 + P

WRU: Water-resistant upper

HRO: Heat-resistant outsole compound tested at 300°C

CI: Cold insulation

A: Electrical resistance (between 0.1-1000 Mega Ohms)

E: Energy absorption in the heel area (tested at 20 Joules)

SRB: Slip-resistance on steel floor with glycerol

BGR 191: Orthopedic footwear adjustment according to German BGR 191. Footwear is tested with adjusted orthopedic insoles in accordance with EN ISO 20345 standard



CE



Aluminium toecap



ESD



Nail protection in plasma-treated composite (PTC) textile



Heat-resistant outsole



Water repellent



Oil-resistant outsole



Ergothon Shock Absorption System



Anti-static properties

The product features remain unchanged only when insoles recommended by the manufacturer are used. All values for the specified product are indicated without tolerances and may vary to actual value for individual products. We reserve the right to modify or update the information in this document without prior notice.

2015-09-29

3(3)

ejendals
PROTECTING HANDS AND FEET

EJENDALS AB

Box 7, SE-793 21 Leksand, Sweden

Phone +46 (0) 247 360 00

Fax +46 (0) 247 360 10

info@ejendals.com

order@ejendals.com

www.ejendals.com