

**Section 1: Identification of the substance/mixture and of the company/undertaking**

**1.1. Product identifier**

**Product name:** RHINO BATHROOM DRAIN UNBLOCKER

**1.2. Relevant identified uses of the substance or mixture and uses advised against**

**Use of substance / mixture:** Consumer use of washing and cleaning products. Industrial use of washing and cleaning products.

**1.3. Details of the supplier of the safety data sheet**

**Company name:** Kilrock Products Ltd  
Units 1b/2b  
Alma Road ind Est  
Chesham  
Buckinghamshire  
HP5 3HB  
United Kingdom  
**Tel:** +44 (0)1494 793900  
**Email:** [velda@kilrock.co.uk](mailto:velda@kilrock.co.uk)

**1.4. Emergency telephone number**

**Emergency tel:** +44 (0)1494 793900  
(office hours only)

**Section 2: Hazards identification**

**2.1. Classification of the substance or mixture**

**Classification under CLP:** Skin Corr. 1A: H314

**Most important adverse effects:** Causes severe skin burns and eye damage.

**2.2. Label elements**

**Label elements:**

**Hazard statements:** H314: Causes severe skin burns and eye damage.

**Signal words:** Danger

**Hazard pictograms:** GHS05: Corrosion



**Precautionary statements:** P101: If medical advice is needed, have product container or label at hand.  
P103: Read label before use.

# SAFETY DATA SHEET

RHINO BATHROOM DRAIN UNBLOCKER

Page: 2

P102: Keep out of reach of children.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

## 2.3. Other hazards

**PBT:** This product is not identified as a PBT/vPvB substance.

## Section 3: Composition/information on ingredients

### 3.2. Mixtures

#### Hazardous ingredients:

##### SODIUM HYDROXIDE

EINECS	CAS	PBT / WEL	CLP Classification	Percent
215-185-5	1310-73-2	-	Skin Corr. 1A: H314	1-10%

##### SODIUM HYPOCHLORITE SOLUTION CL ACTIVE

231-668-3	7681-52-9	-	Skin Corr. 1B: H314; Aquatic Acute 1: H400; -: EUH031	1-10%
-----------	-----------	---	---	-------

##### LAURETH - 11 CARBOXYLIC ACID

-	27306-90-7	-	Skin Irrit. 2: H315; Eye Dam. 1: H318	<1%
---	------------	---	---------------------------------------	-----

## Section 4: First aid measures

### 4.1. Description of first aid measures

**Skin contact:** Remove all contaminated clothes and footwear immediately unless stuck to skin.

Drench the affected skin with running water for 10 minutes or longer if substance is still on skin. Consult a doctor.

**Eye contact:** Bathe the eye with running water for 15 minutes. Transfer to hospital for specialist examination.

**Ingestion:** Wash out mouth with water. Do not induce vomiting. Give 1 cup of water to drink every 10 minutes. Consult a doctor.

**Inhalation:** Remove casualty from exposure ensuring one's own safety whilst doing so.

### 4.2. Most important symptoms and effects, both acute and delayed

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. May cause permanent damage.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

**Inhalation:** There may be shortness of breath with a burning sensation in the throat.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

[cont...]

# SAFETY DATA SHEET

RHINO BATHROOM DRAIN UNBLOCKER

Page: 3

## 4.3. Indication of any immediate medical attention and special treatment needed

**Immediate / special treatment:** Eye bathing equipment should be available on the premises.

## Section 5: Fire-fighting measures

### 5.1. Extinguishing media

**Extinguishing media:** Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

### 5.2. Special hazards arising from the substance or mixture

**Exposure hazards:** Corrosive. In combustion emits toxic fumes.

### 5.3. Advice for fire-fighters

**Advice for fire-fighters:** Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes.

## Section 6: Accidental release measures

### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions:** Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

### 6.2. Environmental precautions

**Environmental precautions:** Do not discharge into drains or rivers. Contain the spillage using bunding.

### 6.3. Methods and material for containment and cleaning up

**Clean-up procedures:** Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

### 6.4. Reference to other sections

**Reference to other sections:** Refer to section 8 of SDS. Refer to section 13 of SDS.

## Section 7: Handling and storage

### 7.1. Precautions for safe handling

**Handling requirements:** Avoid direct contact with the substance. Ensure there is sufficient ventilation of the area. Do not handle in a confined space. Avoid the formation or spread of mists in the air.

### 7.2. Conditions for safe storage, including any incompatibilities

**Storage conditions:** Store in a cool, well ventilated area. Keep container tightly closed.

### 7.3. Specific end use(s)

**Specific end use(s):** PC35: Washing and cleaning products (including solvent based products).

## Section 8: Exposure controls/personal protection

[cont...]

# SAFETY DATA SHEET

RHINO BATHROOM DRAIN UNBLOCKER

Page: 4

## 8.1. Control parameters

**Hazardous ingredients:**

**SODIUM HYDROXIDE**

**Workplace exposure limits:**

**Respirable dust**

State	8 hour TWA	15 min. STEL	8 hour TWA	15 min. STEL
UK	-	2 mg/m <sup>3</sup>	-	-

## DNEL/PNEC Values

**DNEL / PNEC** No data available.

## 8.2. Exposure controls

**Engineering measures:** Ensure there is sufficient ventilation of the area.

**Respiratory protection:** Respiratory protection not required.

**Hand protection:** Impermeable gloves.

**Eye protection:** Safety glasses. Ensure eye bath is to hand.

**Skin protection:** Impermeable protective clothing.

**Environmental:** Refer to specific Member State legislation for requirements under Community environmental legislation.

## Section 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

**State:** Liquid

**Colour:** Pale yellow

**Odour:** Characteristic odour

**Evaporation rate:** Not applicable.

**Oxidising:** Non-oxidising (by EC criteria)

**Solubility in water:** Miscible in all proportions

**Viscosity:** No data available.

**Boiling point/range°C:** 100

**Melting point/range°C:** No data available.

**Flammability limits %: lower:** Not applicable.

**upper:** Not applicable.

**Flash point°C:** Not applicable.

**Part.coeff. n-octanol/water:** No data available.

**Autoflammability°C:** No data available.

**Vapour pressure:** No data available.

**Relative density:** 1.1

**pH:** 14

**VOC g/l:** No data available.

### 9.2. Other information

**Other information:** No data available.

## Section 10: Stability and reactivity

[cont...]

**SAFETY DATA SHEET**  
RHINO BATHROOM DRAIN UNBLOCKER

Page: 5

**10.1. Reactivity**

**Reactivity:** Stable under recommended transport or storage conditions.

**10.2. Chemical stability**

**Chemical stability:** Stable under normal conditions.

**10.3. Possibility of hazardous reactions**

**Hazardous reactions:** Hazardous reactions will not occur under normal transport or storage conditions.  
Decomposition may occur on exposure to conditions or materials listed below.

**10.4. Conditions to avoid**

**Conditions to avoid:** Heat.

**10.5. Incompatible materials**

**Materials to avoid:** Strong oxidising agents. Strong acids.

**10.6. Hazardous decomposition products**

**Haz. decomp. products:** In combustion emits toxic fumes.

**Section 11: Toxicological information**

**11.1. Information on toxicological effects**

**Hazardous ingredients:**

**SODIUM HYDROXIDE**

IPR	MUS	LD50	40	mg/kg
ORL	RBT	LDLO	500	mg/kg

**SODIUM HYPOCHLORITE SOLUTION...100% CL ACTIVE**

ORL	MUS	LD50	8910	mg/kg
-----	-----	------	------	-------

**Relevant hazards for product:**

Hazard	Route	Basis
Skin corrosion/irritation	DRM	Hazardous: calculated
Serious eye damage/irritation	OPT	Hazardous: calculated

**Symptoms / routes of exposure**

**Skin contact:** There may be irritation and redness at the site of contact.

**Eye contact:** There may be irritation and redness. May cause permanent damage.

**Ingestion:** There may be soreness and redness of the mouth and throat. Nausea and stomach pain may occur. There may be vomiting.

**Inhalation:** There may be shortness of breath with a burning sensation in the throat.

**Delayed / immediate effects:** Immediate effects can be expected after short-term exposure.

**Other information:** Not applicable.

[cont...]

**SAFETY DATA SHEET**  
RHINO BATHROOM DRAIN UNBLOCKER

Page: 6

**Section 12: Ecological information**

**12.1. Toxicity**

**Hazardous ingredients:**

**SODIUM HYDROXIDE**

PENAID SHRIMP (Penaeus sp.)	96H LC50	>100	mg/l
-----------------------------	----------	------	------

**SODIUM HYPOCHLORITE SOLUTION...100% CL ACTIVE**

RAINBOW TROUT (Oncorhynchus mykiss)	96H LC50	0.033	mg/l
-------------------------------------	----------	-------	------

**12.2. Persistence and degradability**

**Persistence and degradability:** No data available.

**12.3. Bioaccumulative potential**

**Bioaccumulative potential:** No bioaccumulation potential.

**12.4. Mobility in soil**

**Mobility:** Readily absorbed into soil.

**12.5. Results of PBT and vPvB assessment**

**PBT identification:** This product is not identified as a PBT/vPvB substance.

**12.6. Other adverse effects**

**Other adverse effects:** Negligible ecotoxicity.

**Section 13: Disposal considerations**

**13.1. Waste treatment methods**

**Disposal operations:** Transfer to a suitable container and arrange for collection by specialised disposal company.

**Disposal of packaging:** Dispose of in a regulated landfill site or other method for hazardous or toxic wastes.

**NB:** The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

**Section 14: Transport information**

**14.1. UN number**

**UN number:** UN1760

**14.2. UN proper shipping name**

**Shipping name:** CORROSIVE LIQUID, N.O.S.  
(SODIUM HYDROXIDE, SODIUM HYPOCHLORITE mixture)

[cont...]

**SAFETY DATA SHEET**  
RHINO BATHROOM DRAIN UNBLOCKER

Page: 7

**14.3. Transport hazard class(es)**

**Transport class:** 8

**14.4. Packing group**

**Packing group:** II

**14.5. Environmental hazards**

**Environmentally hazardous:** Yes

**Marine pollutant:** No

**14.6. Special precautions for user**

**Special precautions:** No special precautions.

**Tunnel code:** E

**Transport category:** 2

**Section 15: Regulatory information**

**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

**Specific regulations:** Not applicable.

**15.2. Chemical Safety Assessment**

**Chemical safety assessment:** A chemical safety assessment has not been carried out for the substance or the mixture by the supplier.

**Section 16: Other information**

**Other information**

**Other information:** This safety data sheet is prepared in accordance with Commission Regulation (EU) No 2015/830.

This safety data sheet is prepared in accordance with Commission Regulation (EC) No 1272/2008.

**Phrases used in s.2 and s.3:** EUH031: Contact with acids liberates toxic gas.  
H314: Causes severe skin burns and eye damage.  
H315: Causes skin irritation.  
H318: Causes serious eye damage.  
H400: Very toxic to aquatic life.

**Legal disclaimer:** The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.