Reed Switch





Description

Miniature Heavy Duty Magnetic Proximity Sensor is designed as a general purpose position or movement sensor. It should not be used in or relied on in safety related applications.

Operation and Use

The product is a reed switch based sensor whos contacts change over when in the presence of a magnetic actuator. The non contact operation of these sensors make them suited to applications where misalignment or contamination from dust and solids are a concern. When mounted on or near ferrous surfaces the operating distance will be reduced. Avoid close proximity to strong magnetic fields i.e. electric motors and solenoids. The switch may be operated through a non ferrous skin such as non magnetic stainless steel, plastic, aluminium and non ferrous castings etc. possibly enabling the switch and its connections to be inside part of a housing or machine. The sensors may be operated from three sides.

Specifications

Contact Form : Single Pole Change over

Max. Contact Rating : 5 VA do not exceed product of voltage x amps

Max. Switching Voltage : 75V DC

Max. Switching Current : 0.25 Amps DC resistive
Max. Carry Current : 1 Amps DC resistive

Min. Breakdown Voltage : 200V DC Capacitance : 1pF Contact Resistance : $100m\Omega$

Temperature Range : -10°C to +70°C

Max. Vibration : 30 G's 50-2000 hertz's Max Shock : 50 G's 11ms ½ sine wave

Resonate Frequency : 11,000Hz
Pull in Time : 0.7 ms
Release Time : 1 ms
Environmental Protection : IP65


Operating distance AM/5 : Make 13mm release 19mm nominal Operating distance AM/8 : Make 20mm release 29mm nominal

Cable : 0.5 metres of black round 7-2-3A DEF61-12


Connections : Blue = com, green = n/o, red = n/c


Housing Material : Diecast zinc

Operating positions



Schematic diagram





Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro




Reed Switch



Dimensions

Both the switch and actuator have the same dimensions.



Dimensions: Millimetres

Part Number Table

Description	Part Number
Reed Switch, Flange, 9mm, SPDT, 3 VA, 175V DC, 0.25A	C/03/M

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro Farnell.com/multicomp-pro Element14.com/multicomp-pro

