








## **Model Number**

#### NMB10-18GM65-E3-V1

#### **Features**

- · 10 mm flush
- · Stainless steel sensing face
- Increased operating distance

#### Connection



## **Pinout**



Wire colors in accordance with EN 60947-5-2

1	l BN	(brown
2	WH	(white)
3	BU	(blue)
4	BK	(black)

## **Accessories**


V1-G-2M-PUR

Cable socket, M12, 4-pin, PUR cable

V1-W-2M-PUR

Cable socket, M12, 4-pin, PUR cable

#### **Dimensions**



## **Technical Data**

General specifications		
Switching element function		PNP NC
Rated operating distance	s <sub>n</sub>	10 mm
Installation		flush (Requirements: see drawing below)
Output polarity		DC
Assured operating distance	sa	0 8.1 mm
Actuating element		Ferrous and nonferrous targets
Reduction factor r <sub>Al</sub>		0.4
Reduction factor r <sub>Cu</sub>		0.25
Reduction factor r <sub>304</sub>		0.85
Reduction factor r <sub>St37</sub>		1
Nominal ratings		

Functional safety related parameters

 MTTF<sub>d</sub>
 880 a

 Mission Time (T<sub>M</sub>)
 20 a

 Diagnostic Coverage (DC)
 0 %

Ambient conditions
Ambient temperature -25 ... 70 °C (-13 ... 158 °F)

Mechanical specificationsConnection typeDevice connector M12 x 1 , 4-pinHousing materialStainless steel 1.4305 / AISI 303Sensing faceStainless steel 1.4305 / AISI 303

Sensing face Stainless steel 1.4305 / AISI 303
Protection degree IP67 / IP68 / IP69K - cordset dependent according to cable speci-

# Compliance with standards and directives


Standard conformity

Standards

EN 60947-5-2:2007
IEC 60947-5-2:2007

Approvals and certificates

UL approval cULus Listed, General Purpose
CSA approval cCSAus Listed, General Purpose
CCC approval Products with a maximum operating voltage of ≤36 V do not bear a
CCC marking because they do not require approval.



Sensor face is flush with mounting surface.

www.pepperl-fuchs.com