

Quick-change steel tool holder

Application:


For holding change tool holders. The selection of the Multifix quick-change steel tool holder and change tool holder depends on the drive output, the tool carriage width and lathe chisel height.

Version:

- The drill hole in the centring disc must be enlarged to the dimensions of the clamping screw.

Advantage:

- Precision manufacture owing to the high repeat accuracy (0.01 mm)
- Versatile production possibilities (40 tool positions possible)
- Quick and trouble-free height adjustment thanks to adjusting screw
- Extremely flexible due to the modular structure



Art. no.	22240 080
Steel holder head size	C
Changeover holder size	CD 32, CD 40, CD 45
Max. drive power of lathe	13.2 kW
Max. carriage width	180 mm
Steel support	16.5 mm
Drill hole	16 mm
Max. bore diameter	55 mm
Normal hole diameter	40 mm
Max. boring depth	75 mm
Height	105 mm
Max. steel holder width	202 mm
Max. throat depth/holder width	102 mm

EAN-Code

4039247141524