

Screw extractor, individual, M 5 to M 30

For right-hand and left-hand threads

RENNSTEIG

Application:

For damage-free extraction of broken screws or bolts.

Version:

- Non-slip, twin-edged intrusion in the damaged screw
- Burnished surface
- Polished cutting surface
- Patented version

Advantage:

- With centre punch tip and hexagonal shoulder
- For right-hand and left-hand threads



Art. no.	55004 030
Suitable for min./max. thread	M10-M12
Min./max. pilot hole diameter	6.4-9.5 mm

EAN-Code

4049002020896