



Part no.: 50105153
TKS 50X50.1
Reflector

Figure can vary

Contents

- Technical data
- Accessories

Part no.: 50105153 – TKS 50X50.1 – Reflector

Technical data

Mechanical data	
Design	Rectangular
Mounting dimension, width	51.4 mm
Reflection surface width	47 mm
Mounting dimension, height	60.3 mm
Reflection surface height	48 mm
Mounting dimension, thickness	8.5 mm
Triple reflector size	4 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PMMA8N
Structure, active surface	Triple
Net weight	18 g
Type of fastening	Adhesive Through-hole mounting


Environmental data	
Ambient temperature, operation	-40 ... 65 °C

Certifications	
Degree of protection	IP 67

Classification	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

Accessories

Mounting technology - Rod mounts

	Part no.	Designation	Article	Description
	50117252	BTU 300M-D12	Mounting system	Contains: 2x M4 x 25 screw, 2x M4 x 20 screw, 4x position washers Design of mounting device: Mounting system Fastening, at system: For 12 mm rod, Sheet-metal mounting Mounting bracket, at device: Screw type, Suited for M4 screws Type of mounting device: Clampable, Adjustable, Turning, 360° Material: Metal

Note
A list with all available accessories can be found on the Leuze electronic website in the Download tab of the article detailed page.