


NOTES:

1. MATERIALS AND FINISHES:
 BODY - BRASS, NICKEL PLATING
 BAYONET - ZINC DIECAST, NICKEL PLATING
 CONTACT - BRASS, GOLD PLATING
 INSULATOR - DELRIN
2. ELECTRICAL:
 A. IMPEDANCE: 50 OHM
 B. FREQUENCY RANGE: DC 0-4 GHz
 C. VSWR(RETURN LOSS): 1.5 MAX.
3. MECHANICAL:
 A. DURABILITY: 500 CYCLES MIN.
 B. TEMPERATURE RANGE: - 55°C to +165°C
4. CRIMPED FERRULE
 HEX CRIMP SIZE .255"
5. CONTACT PIN TO SOLDER

31-6005-RFX		REVISIONS			
PART NO	REV	DESCRIPTION	DATE	ECO	APPR
THIRD ANGLE PROJ.	B	BAYONET WAS BRASS	1/13/06	46154	GII



CUSTOMER OUTLINE DRAWING
 ALL OTHER SHEETS ARE FOR INTERNAL USE ONLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN METRIC AND TOLERANCES ARE: 0.5 - 6mm ±0.1mm 6 - 30mm ±0.2mm 30 - 250mm ±0.3mm ANGLES ±1°	MATERIAL	DRAWN: CARRA ENGINEER	DATE: 23-Jun-06 DATE: 23-Jun-06	TITLE: BNC R/A CRIMP PLUG (FOR BELDEN RG-8/X, TIMES -MR 24CMA)		Amphenol RF January CT, USA, Taichung Taiwan, Shenzhen China www.amphenorf.com	
	REFERENCE	APPROVED: <i>A. Carra</i> DATE: 7/13/06 CAD FILE: F:\GWS\B\1112B4\8X-50\ND552	SCALE: 3/4 DWG SIZE: B	SHEET: 2 OF 2 CODE ID: 74868	REV: B	DRAWING NO: B1112B4-ND3G-8X-50 ITEM NO: 01112ABB89ND5F PART NO: 31-6005-RFX	