




# CXLW-4.8



## Application

- Fastening of overlaps of profile sheets
- Fastening of flashings onto sandwich panels
- Fastening of metal profile sheets onto timber
- Fastening of flashing onto profile sheets
- Fastening of flashing onto sandwich panels

## Fastener material

- Austenitic stainless steel A2
- Sealing washer: Aluminium, EPDM-seal

## Component 1 (t<sub>I</sub>)

Steel	0.40–1.00
Steel	2×0.40–0.63
Steel	2×0.40–1.00

## Component 2 (t<sub>II</sub>)

Steel	0.40–1.00
Steel	2×0.40–0.63
Timber	≥25.0

## Σ<sub>max</sub> t<sub>I</sub>+t<sub>II</sub>

2.00
2.50
–

## Approvals


–

## Features and Benefits

- Fast and chip-free installation thanks to the Speed-Point
- Self drilling fastener suitable for fastening of overlaps and flashings
- Hybrid fastener suitable for fastening onto metal and timber substructure
- No scratches on painted metal surfaces thanks to the sharp Speed-Point
- Secured against unwinding given by cut-off thread-end and free-spin zone
- No torque control required given by free-spin zone
- Cost saving installation due to pre-drilling of metal sheets no longer necessary
- High quality EPDM sealing washer for long-term weather sealing
- For roof applications with drill pressure of 300 N (30 kg) the new CXLW-4.8 can drill through 2×1.25 mm steel sheets


## Documentation

Approval document (ETA) | Declaration of performance (DoP)



## Fastener in A2 onto steel and timber

Product code	PU	L	CL <sub>lap</sub>	CL <sub>timb</sub>	A12	A10
CXLW-D10-A10-4,8×28-A2	250	28	0.40–2.50	16	–	1655713
CXLW-D10-A10-4,8×28-A2-RAL7024	250	28	0.40–2.50	16	–	1655745
CXLW-D10-A10-4,8×28-A2-RAL9006	250	28	0.40–2.50	16	–	1655748



## Accessories/Ancillaries

Product code	PU	
T20W-25-HEX ¼"	10	895280
Bit holder ZA ¼"	10	1162306