


FT-30-P-A-M8

Fibre optics



Product characteristics  
Diffuse reflection sensor

M8

Range 70 mm

Connection to fibre optic amplifiers type OIF

Range

Range	OIF: 70 mm
-------	------------

Environment

Ambient temperature [°C]	-20...80
--------------------------	----------

Mechanical data

Design	straight
--------	----------

Length [mm]	600
-------------	-----

Min. bending radius [mm]	30
--------------------------	----

Fiber arrangement



Fibre optic

glass

Sensing head

aluminium

Sheathing

PVC; adapter: polyamide

Weight [kg]

0.09

Accessories

Accessories (included)	2 hexagon nuts; M8; stainless steel; 2 tooth lock washers; 1 knurled nut; M30
------------------------	---

Remarks

Pack quantity [piece]	1
-----------------------	---