


## Switched-Mode Power Supply, 1-Phase

EPSITRON® PRO Power



- Primary switch mode power supply unit with PowerBoost and TopBoost
- Stand-by input for switching off the output and minimizing power consumption
- DC OK contact for output monitoring
- Parallel operation, series connection possible
- Prepared for class I equipment
- Natural convection cooling when horizontally mounted
- Enclosed for use in switchgear cabinets
- Electrically isolated output voltage (SELV) acc. to EN 60950-1/UL 60950

Description	Item No.	Pack. Unit
Switched-Mode Power Supply, 48 V DC / 10 A	787-835	1

Technical Data	
<b>Input:</b>	
Nominal input voltage $V_i$ nom	110 ... 240 VAC
Input voltage range	85 ... 264 VAC; 120 ... 350 VDC
Input voltage derating	-1.5 % / V AC < 110 VAC
Frequency	50 Hz ... 60 Hz
Input current $I_i$	2.3 A at 230 VAC and 10 ADC
Discharge current	1 mA typ.
Inrush current	< 8 A (active inrush current limitation)
Mains failure hold-up time	20 ms typ. at 230 VAC
<b>Output:</b>	
Nominal output voltage $V_o$ nom	48 VDC (SELV)
Output voltage range	33 ... 52 VDC adjustable
Output current $I_o$	10 A at 48 V DC
PowerBoost	17.5 ADC (for 4 s); 15 ADC (for 8 s)
TopBoost	60 ADC (for 25 ms)
Factory preset	48 VDC
Adjustment accuracy	1%
Residual ripple	< 70 mV (peak-peak)
Current limitation	1.1 x $I_o$ typ.
Overload behavior	TopBoost / PowerBoost / Constant current
Operational indication	LED green (DC O.K.), LED red (error)
Signaling	Relay contact DC O.K. (changeover contact)
<b>Efficiency / power losses:</b>	
Efficiency	91 % typ.
Power loss $P_V$	0.8 W (stand-by) / 4.8 W (no load) / 43.2 W (rated load)
<b>Fuse protection:</b>	
Internal fuse	T 10 A / 250 V
External fuse	Circuit breakers 6 A, 10 A, 16 A, characteristic: B or C
	An external DC fuse is required for the DC input voltage

Technical Data	
<b>Environmental requirements:</b>	
Ambient operating temperature	-25 °C ... +70 °C
Storage temperature	-25 °C ... +85 °C
Rel. humidity	30 % ... 85 % (no condensation)
Derating	-3 % / K (> +50 °C)
Degree of pollution	2 (acc. to EN 50178)
Climatic category	3K3 (acc. to EN 60721)
<b>Safety and protection:</b>	
Test voltage pri.-sec./ pri.-gr. / sec.-gr.	4.2 kV DC / 2.2 kV DC / 0.7 kV DC
Protection class	Prepared for class I equipment
Degree of protection	IP20 (acc. to EN 60529)
Overvoltage protection	via varistor at primary circuit
Short circuit protection	yes
No-load proof	yes
Feedback voltage	max. 63 VDC
Parallel operation	yes
Series connection	yes
<b>Connection and type of mounting:</b>	
Wire connection	Input: WAGO 231 Series Output: WAGO 831 Series Signalling: WAGO 733 Series
Cross sections	Input: 0.08 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> / AWG 28 ... 12 Output: 0.5 mm <sup>2</sup> ... 10 mm <sup>2</sup> / AWG 20 ... 8 Signalling: 0.08 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> / AWG 28 ... 20
Strip lengths	Input: 8 ... 9 mm / 0.33 in Output: 13 ... 15 mm / 0.55 in Signalling: 5 ... 6 mm / 0.22 in
Type of mounting	DIN-rail mounting (EN 60715) in 2 positions
<b>Dimensions and weight:</b>	
Dimensions (mm) W x H x L	97 x 171 x 187 (incl. female connector) Length from upper-edge of DIN 35 rail
Weight	2460 g
<b>Standards and approvals:</b>	
Standards/Specifications	EN 60950, EN 61204-3, UL 60950, UL 508