


## British Standard Roller Chains



### Product Definition

Our chains comply with European standard (DIN 8187-ISO 606). These chains are made from carbon steel. The plates are heat treated (42 to 46 HRC), the axles are cabonitrided and the chains are pre-stretched. Temperature of use between -50°C and +100°C.



ISO	Pitch	P (mm)	b1 min (mm)	D max (mm)	d (mm)	L1 (mm)	L2 (mm)	h (mm)	t (mm)	Min Tensile strength Q min Kn	Weight per MTR
081	1/2"	12.70	3.30	7.75	3.66	5.1	5.1	9.91	1.00	8.20	0.29
083	1/2"	12.70	4.88	7.75	4.09	6.45	6.45	10.30	1.27	12.00	0.43
084	1/2"	12.70	4.88	7.75	4.09	7.40	7.40	11.15	1.80	16.00	0.60