# **Coaxial Cable**



## RoHS Compliant



## **Specifications**

#### Designed of cable

Inner Conductor : 1/1.02 ±0.01mm Copper Clad Steel

Insulation : Foamed PE

Insulation Colour : White

Size of Insulation :  $\emptyset$ 4.7 ±0.1mm Wall Thickness :  $\approx$ 1.8 mm Screening : AL Foil

Braiding : 16×4/0.12 ±0.003mm AL/MG

Jacket : PVC Jacket Colour : White

Jacket Size : Ø6.8 ±0.2mm Jacket Wall Thickness : ≈0.8mm

Electric data at 20°C

Conductor Resistance :  $\leq 120\Omega/KM$ Insulation Resistance :  $\geq 5000M\Omega^*KM$ 

Testing Voltage : wire/wire/screen 50Hz 1min=1.5kV

Impedance :  $75 \pm 3\Omega$  at 200MHz

ATT max less than 10%:

Frequency	50	100	200	800	1000
ATT dB/100m	9.8	11	12.5	18.5	22.5

Zo : 75±3 Ohmat 200Mhz

Co : 55pF/m RL : ≥20dB

Temperature Range : -10°C to +60°C

### **Part Number Table**

Description	Part Number	
RG6U Coaxial Cable, Black, 10m	14802 10M	

Important Notice: This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of Premier Farnell Limited 2019.

Newark.com/exclusive-brands Farnell.com/exclusive-brands Element14.com/exclusive-brands

