

SLCD-61N8

Solderable Planar Photodiode

Features


- Visible to IR spectral irradiance range
- High reliability
- Oxide passivation
- Linear short circuit current
- Low capacitance, high speed
- Available in arrays where # indicates number of elements (maximum of 8 elements)

Description


The Silonex series of silicon solderable planar photodiodes feature low cost, high reliability, and linear short circuit current over a wide range of illumination. These devices are widely used for light sensing and power generation because of their stability and high efficiency. They are particularly suited to power conversion applications due to their low internal impedance and relatively high shunt impedances, and stability. These devices also provide a reliable, inexpensive detector for applications such as light beam sensing and instrumentation. The electrical characteristics below are per element. In the multielement arrays the cathodes are common to a all elements.

Absolute Maximum Ratings

Storage Temperature	-40°C to +125°C
Operating Temperature	-40°C to +125°C



Also available with leads as part number SLSD-71N8



Symbol	Parameter	Min	Тур	Max	Units	Test Conditions
I _{SC}	Short Circuit Current	100	170		μΑ	$V_{R}=0V, Ee=25mW/cm^{2}$ (1)
V _{oc}	Open Circuit Voltage		0.40		V	$Ee=25mw/cm^2$ (1)
I _D	Reverse Dark Current			1.7	μA	V _R =5V, Ee=0
CJ	Junction Capacitance		100		pF	V _R =0V, Ee=0, f=1MHz
S_λ	Spectral Sensitivity		0.55		A/W	λ=940nm
V_{BR}	Reverse Breakdown Voltage	20			V	I _R =100μA
λ _P	Maximum Sensitivity Wavelength		930		nm	
λ_{R}	Sensitivity Spectral Range	400		1100	nm	
$\theta_{1/2}$	Acceptance Half Angle		60		deg	

Electrical Characteristics (T_A=25°C unless otherwise noted)

Specifications subject to change without notice

104118 REV 0

Notes: (1) Ee = light source @ 2854 °K