

#### 8.89mmx3.81mm LED LIGHT BAR

P/N: KB-2400YW

YELLOW


#### **Features**


- •UNIFORM LIGHT EMITTING AREA.
- •LOW CURRENT OPERATION.
- ●EASILY MOUNTED ON P.C. BOARDS.
- •FLUSH MOUNTABLE.
- •CAN BE USED WITH PANELS AND LEGEND MOUNTS.
- ●RoHS COMPLIANT.


#### Description


The Yellow source color devices are made with Gallium Arsenide Phosphide on Gallium Phosphide Yellow Light Emitting Diode.

# Package Dimensions & Internal Circuit Diagram









PAGE: 1 OF 3

#### Notes

- 1. All dimensions are in millimeters (inches), Tolerance is  $\pm 0.25 (0.01")$  unless otherwise noted.
- 2. Specifications are subject to change without notice.

SPEC NO: DSAB2140 REV NO: V.7 DATE: NOV/19/2005
APPROVED: J. Lu CHECKED: Joe Lee DRAWN: Y.L.LI

# Kingbright

### **Selection Guide**

| Part No.  | Dice               | Lens Type      | lv (mcd)<br>@ 20mA |      |
|-----------|--------------------|----------------|--------------------|------|
|           |                    |                | Min.               | Тур. |
| KB-2400YW | YELLOW (GaAsP/GaP) | WHITE DIFFUSED | 7                  | 40   |

## Electrical / Optical Characteristics at Ta=25°C

| Symbol | Parameter                | Device | Тур. | Max. | Units | Test Conditions |
|--------|--------------------------|--------|------|------|-------|-----------------|
| λpeak  | Peak Wavelength          | Yellow | 590  |      | nm    | I==20mA         |
| λD     | Dominant Wavelength      | Yellow | 588  |      | nm    | IF=20mA         |
| Δλ1/2  | Spectral Line Half-width | Yellow | 35   |      | nm    | IF=20mA         |
| С      | Capacitance              | Yellow | 20   |      | pF    | VF=0V;f=1MHz    |
| VF     | Forward Voltage          | Yellow | 2.1  | 2.5  | V     | I==20mA         |
| IR     | Reverse Current          | Yellow |      | 10   | uA    | VR = 5V         |


### Absolute Maximum Ratings at TA=25°C

| Parameter                                       | Yellow         | Units |
|---|----------------|-------|
| Power dissipation                               | 105            | mW    |
| DC Forward Current                              | 30             | mA    |
| Peak Forward Current [1]                        | 140            | mA    |
| Reverse Voltage                                 | 5              | V     |
| Operating / Storage Temperature                 | -40°C To +85°C |       |
| Lead Solder Temperature [2] 260°C For 5 Seconds |                |       |

1. 1/10 Duty Cycle, 0.1ms Pulse Width.
 2. 2mm below package base.


SPEC NO: DSAB2140 **REV NO: V.7** DATE: NOV/19/2005 PAGE: 2 OF 3 APPROVED: J. Lu **CHECKED:** Joe Lee DRAWN: Y.L.LI


# **Kingbright**





Yellow

**KB-2400YW** 









#### Remarks

If special sorting is required (e.g. binning based on forward voltage, Luminous intensity/ luminous flux, or wavelength), the typical accuracy of the sorting process is as follows:

- 1. Wavelength: +/-1nm
- 2. Luminous intensity/ Luminous Flux: +/-15%
- 3. Forward Voltage: +/-0.1V

Note: Accuracy may depend on the sorting parameters.

SPEC NO: DSAB2140 REV NO: V.7 DATE: NOV/19/2005 PAGE: 3 OF 3
APPROVED: J. Lu CHECKED: Joe Lee DRAWN: Y.L.LI