


REV. 1 4/26/95

COIL:  $\bullet$  +25 °C  
 RESISTANCE 160 OHMS ± 10%  
 NOMINAL VOLTAGE 12.0 VDC  
 MUST OPERATE 7.2 VDC  
 MUST RELEASE 4.0 VDC MAX, .7 VDC MIN.

CUSTOMER DATA SHEET



ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 100 g's 6 ± 1 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

CONTACT RATING: LOW LEVEL TO 2A  
28 VDC RESISTIVE 100,000 OPERATIONS

NOTES: MAXIMUM TRANSIENT SUPPRESSED VOLTAGE  
OF -24 VDC WITH BIFILAR COIL  
OPERATE & RELEASE 5 MS MAX.  
CONTACT STABILIZATION 2.5 MS MAX.

DR. R.B. 5/27/94 CK. *ALGOS*



CUST. OPL  
 CUST. NO. M39016/22-016P

TYPE "HMB" RELAY

HMB1201G01P