

Load cells SAUTER CP P2 · CP P8 · CP P7 · CP P9









CP P2 · CP P8

Single-point load cell of aluminium

CP P7

Single-point load cells of Stainless steel

CP P9

Single-point load cells of stainless steel



· RoHS compliant

· Aluminium, anodised

bench scales, etc.

400×400 mm

450×450 mm



Dust and spray protection to IP65

· Suitable for price-computing scales,

• Maximum platform size 100-300 kg:

• Maximum platform size 400-500 kg:

• Nominal sensitivity: 2 mV/V

· Note: Version in accordance with

OIML R60 C4 or C5 on request

(in accordance with EN 60529)



Accuracy in accordance with OIML R60 C3





- · Accuracy in accordance with OIML R60 C3
- · RoHS compliant
- Dust and spray protection to IP67 (in accordance with EN 60529)
- · Stainless steel
- · Application example: Weight as well as compressive force measurements under harsh environmental conditions
- · Suitable for bench scales, price-computing scales
- · Maximum platform size 400×400 mm
- 6-wire connection

Model

- · Nominal sensitivity: 2 mV/V
- · Note: Version in accordance with OIML R60 C4 on request

TANDARD			
566	444	M	
ID CO	IDCOK		





- Accuracy in accordance with OIML R60 C3
- · RoHS compliant
- Dust and spray protection to IP68/IP69K (in accordance with EN 60529), welded to create a hermetic seal
- · Stainless steel
- · Area of application: Weight measurement as well as compressive force in harsh environments
- · Suitable for platform scales, checkweighers
- Maximum platform size 10-50 kg: 400×400 mm
- Maximum platform size 100-500 kg: 800×800 mm
- 4-wire connection (10-50 kg)
- 6-wire connection (100-500 kg)
- Nominal sensitivity: 2 mV/V
- · Note: Version in accordance with OIML R60 C4 or C5 on request

Model	Nominal load
SAUTER	kg
CP 100-3P2	100
CP 150-3P2	150
CP 200-3P2	200
CP 300-3P2	300
CP 400-3P2	400
CP 500-3P2	500
CP 50-3P8	50
CP 100-3P8	100
CP 150-3P8	150
CP 200-3P8	200
CP 250-3P8	250
CP 300-3P8	300
CP 500-3P8	500
CP 600-3P8	600
Market Land	

Model	Nominal load	
KERN	kg	
CP 30-3P7	30	
CP 50-3P7	50	
CP 75-3P7	75	
CP 100-3P7	100	
CP 150-3P7	150	

Nominal load

Model	Nominal load	
SAUTER	kg	
CP 10-3P9	10	
CP 20-3P9	20	
CP 50-3P9	50	
CP 100-3P9	100	
CP 200-3P9	200	
CP 300-3P9	300	
CP 400-3P9	400	
CP 500-3P9	500	

■ ONLY WHILE STOCKS LAST!





Further details and technical data sheet as well as extensive accessories see internet

MEASURING TECHNOLOGY & TEST SERVICE 2023

SAUTER PICTOGRAMS





Adjusting program (CAL):

For quick setting of the instrument's accuracy. External adjusting weight required



Calibration block:

Standard for adjusting or correcting the measuring device



Peak hold function:

Capturing a peak value within a measuring process



Scan mode:

Continuous capture and display of measurements



Push and Pull:

The measuring device can capture tension and compression forces



Length measurement:

Captures the geometric dimensions of a test object or the movement during a test process



Focus function:

Increases the measuring accuracy of a device within a defined measuring range



Internal memory:

To save measurements in the device memory



Data interface RS-232:

Bidirectional, for connection of printer and PC



Profibus:

For transmitting data, e.g. between scales, measuring cells, controllers and peripheral devices over long distances. Suitable for safe, fast, fault-tolerant data transmission. Less susceptible to magnetic interference.



Profinet:

Enables efficient data exchange between decentralised peripheral devices (balances, measuring cells, measuring instruments etc.) and a control unit (controller). Especially advantageous when exchanging complex measured values, device, diagnostic and process information. Savings potential through shorter commissioning times and device integration possible



Data interface USB:

To connect the measuring instrument to a printer, PC or other peripheral devices



Bluetooth* data interface:

To transfer data from the balance/ measuring instrument to a printer, PC or other peripherals



WLAN data interface:

To transfer data from the balance/ measuring instrument to a printer, PC or other peripherals



Data interface Infrared:

To transfer data from the measuring instrument to a printer, PC or other peripheral devices



Control outputs

(optocoupler, digital I/O):

To connect relays, signal lamps, valves, etc.



Analogue interface:

To connect a suitable peripheral device for analogue processing of the measurements



Analog output:

For output of an electrical signal depending on the load (e.g. voltage 0 V - 10 V or current 4 mA - 20 mA)



Statistics:

Using the saved values, the device calculates statistical data, such as average value, standard deviation etc.



PC Software:

To transfer the measurement data from the device to a PC



Printer:

A printer can be connected to the device to print out the measurement



Network interface:

For connecting the scale/measuring instrument to an Ethernet network



KERN Communication Protocol (KCP):

It is a standardized interface command set for KERN balances and other instruments, which allows retrieving and controlling all relevant parameters and functions of the device. KERN devices featuring KCP are thus easily integrated with computers, industrial controllers and other digital systems



GLP/ISO record keeping:

Of measurement data with date, time and serial number. Only with SAUTER printers



Measuring units:

Weighing units can be switched to e.g. non-metric. Please refer to website for more details



Measuring with tolerance range (limit-setting function):
Upper and lower limiting can be programmed individually. The process is supported by an audible or visual signal, see the relevant model



Protection against dust and water splashes IPxx:

The type of protection is shown in the pictogram cf. DIN EN 60529:2000-09, IEC 60529:1989+A1:1999+A2:2013



ZERO:

Resets the display to "0"



Battery operation:

Ready for battery operation. The battery type is specified for each device



Rechargeable battery pack:

Rechargeable set



Plug-in power supply:

230V/50Hz in standard version for EU. On request GB, AUS or USA version available



Integrated power supply unit: Integrated, 230V/50Hz in EU.

More standards e.g. GB, AUS or USA on request



Motorised drive:

The mechanical movement is carried out by a electric motor



Motorised drive:

The mechanical movement is carried out by a synchronous motor (stepper)



Fast-Move:

The total length of travel can be covered by a single lever movement



Verification possible:

Models with type approval for construction of verifiable systems



DAkkS calibration possible:

The time required for DAkkS calibration is shown in days in the pictogram



Factory calibration:

The time required for factory calibration is specified in the pictogram



Package shipment:

The time required for internal shipping preparations is shown in days in the



Pallet shipment:

The time required for internal shipping preparations is shown in days in the pictogram

^{*}The Bluetooth® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by KERN & SOHN GmbH is under license. Othear trademarks and trade names are those of their respective owners.