

Machine tap extension with internal cooling and h6 shank

For the use of machine taps with internal cooling

ORION[®]

Application:

For extending machine taps in conjunction with deep and difficult to reach threads on CNC and conventional machines, in tapping chucks or quick-change chucks in single part production.



Version:

- Steel tool holder with collet chuck and clamping nut h6 shank, steel shank of the extension pursuant to DIN for high requirements for process reliability and service life

Advantage:

- Very flexible and fast solution as there is no need to procure special machine taps
- User-friendly handling and short retooling times
- Excellent value for money

| | |
|--|------------------|
| Art. no. | 13533 523 |
| Suitable for DIN 374/376 screw tap | M20-M24 |
| Suitable for screw tap square socket size | 14.5 mm |
| Size of square | 14.5 mm |
| Collect depth | 47 mm |
| Collet chuck diameter | 18 mm |
| Collect outer diameter | 26 mm |
| Shaft diameter | 18 mm |
| Length | 330 mm |
| Shaft length | 100 mm |

EAN-Code

4053625475704