




TE Internal #: 1735284-4

SATA, Receptacle, Cable-to-Board, 22 Position, 7P + 15P, Standard Connector Profile, Vertical, Surface Mount, Height Above PC Board .26 in [6.6 mm]

[View on TE.com >](#)

Connectors > Audio & Video Connectors > SATA & Micro SATA



SATA Connector Type: **SATA**

Connector & Housing Type: **Receptacle**

Connector System: **Cable-to-Board**

Number of Positions: **22**

Contact Configuration: **7P + 15P**

## Features

### Product Type Features

Shell	Without
SATA Connector Type	SATA
Connector & Housing Type	Receptacle
Connector System	Cable-to-Board
Connector & Contact Terminates To	Printed Circuit Board

### Configuration Features

Stackable	No
Number of Positions	22
PCB Mount Orientation	Vertical
Number of Rows	1
Number of Ports	2

### Body Features

Connector Profile	Standard
-------------------	----------

### Contact Features

--	--



Contact Mating Area Plating Material Thickness	.38 $\mu\text{m}$ [15 $\mu\text{in}$ ]
Contact Mating Area Plating Material	Gold
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Configuration	7P + 15P
Contact Current Rating (Max)	1.5 A

### Termination Features

Termination Method to Printed Circuit Board	Surface Mount
---	---------------

### Mechanical Attachment

PCB Mount Retention Feature Length	.8 mm[.032 in]
Mating Alignment Type	Polarization
PCB Mount Retention	With
PCB Mount Retention Type	Solder Peg
PCB Mount Location	Top
Connector Mounting Type	Board Mount

### Housing Features

Housing Material	High Temperature Thermoplastic
Housing Color	Black
Centerline (Pitch)	1.27 mm[.05 in]

### Dimensions

PCB Thickness (Recommended)	1.2 mm[.048 in]
Height Above PC Board	6.6 mm[.26 in]

### Usage Conditions

High Temperature Housing	Yes
Operating Temperature Range	-40 – 85 $^{\circ}\text{C}$ [-40 – 185 $^{\circ}\text{F}$ ][-40 – 185 $^{\circ}\text{F}$ ]

### Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

### Packaging Features

Packaging Quantity	48
Packaging Method	Box & Tray, Tray



Other

SATA Connectors Comment	Low Profile Backplane
-------------------------	-----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Customers Also Bought



TE Part #1-1969688-4  
POWER TRIPLE LOCK HIGH TEMP  
HEADER



TE Part #1-213825-7  
CPC SERIES 1 POSTED



TE Part #1-1734775-1  
Std USB Type A, Flag, T/H, 1.8A



TE Part #1-1825027-1  
FSMRA4JH04=R/A,TACT PB SW,160G



TE Part #1735284-3  
SATA BACKPLANE RECEPTACLE,  
VERTICAL, SMT



TE Part #1735284-2  
SATA BACKPLANE RECEPTACLE,  
VERTICAL, SMT



TE Part #1551920-2  
zQSFP+ connector assembly



TE Part #T4171110504-001  
M12 Panel Mount Wire



TE Part #1473005-4  
DDR2 SO DIMM Sockets



TE Part #1734261-3  
AMP HPI 1.25MM HEADERS

## Documents

### Product Drawings

[SATA BACKPLANE RECEPTACLE, VERTICAL, SMT](#)

English

### CAD Files

[3D PDF](#)

3D

Customer View Model

[ENG\\_CVM\\_CVM\\_1735284-4\\_D.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1735284-4\\_D.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1735284-4\\_D.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications



### Product Specification

English

---

### Product Environmental Compliance

#### TE Material Declaration

English

---

### Agency Approvals

#### UL Report

English