

SVVC steel boring bar, positive left

For longitudinal and copy turning with VC indexable insert

ATORN[®]



Application

For longitudinal and copy turning with VC indexable insert 55°

Version

- Precision-manufactured boring bar, **steel**, with internal cooling, type V, pitch angle 72.5°, tip angle 35°, clearance angle 7°

Advantage

- Slender geometry for longitudinal and copy turning
- Positive geometry for the body ensures low cutting forces

Art. No.	17827 410
ISO name	A 16M SVVC R/L 07
Min. bore diameter	17.5 mm
Shaft diameter	16 mm
Cutting edge height	9.5 mm
Clearance length	36 mm
Length	150 mm
Clamping surface height	15 mm
Programming size	11 mm
Suitable for indexable inserts	VC.. 0702..
Tool design	Left
DIN	8024

EAN-Code

4050293390711