

Tapping chuck, type DSPL

With Morse taper to DIN 228



Application:

For cutting internal threads on reversible drills, lathes and milling machines. Can be used horizontally and vertically.

Execution:

- With Morse taper shank and flat tangs in accordance with DIN 228 B.
- With patented double chuck (clamps shank and square drive).
- Elastic length compensation under compression and tension
- Axial-parallel pendulum device and flexible length compensation for cutting exact gradients and flush threads.
- With clockwise and anti-clockwise rotation.

Delivery:

1x DSPL tapping chuck.



Art. no.	21520 010
Brand	BILZ
Manufacturer Part Number	6707468
Size	DSPL 12
Suitable for thread	M3-M12
Min. clamping range diameter	2.5 mm
Max. clamping range diameter	10 mm
Axial length compensation	20 mm
Morse taper size	MK 2
Projecting length	135 mm
Compensation parallel to axis	1 mm
Gross Weight	1.757 kg
Product Group	2AH

EAN

4039247138579