



MSR Hot Restrike

MSR 200 HR

Thanks to an optimized color temperature and a high color rendering index, the MSR Hot Restrike creates perfect 'daylight' in any condition. Also, the single ended lamp design enables hot re-ignition, which ensures daylight lighting and superb color rendition is always instantly available. They also incorporate the innovative P3 technology, developed by Philips, which allows use at higher temperatures and therefore extends lifetime and consistency of high-quality light output.

Product data

• General Characteristics

System Description	Hot Restrike
Cap-Base	GZY9.5
Cap-Base Information	-
Execution	-
Operating Position	any
Main Application	Studio/Theatre
Life to 50% failures	200 hr
EM	
Non-household	For professional use only-not for domestic use
Symbol	

• Light Technical Characteristics

Color Code	-
Color Rendering Index	92 Ra8
Color Temperature	6000 K
Color Temperature Technical	5900 K
Chromaticity Coordinate X	325 -
Chromaticity Coordinate Y	323 -
Luminous Flux Lamp EM	12000 (min), 15000 (nom) Lm
Luminous Efficacy Lamp EM	75 Lm/W

• Electrical Characteristics

Lamp Wattage	200 W
Lamp Wattage Technical	200 W
Lamp Current	3.3 A

Ignition Supply Voltage	207 (min) V
Dimmable	Yes

• Luminaire Design Requirements

Pinch Temperature	350 (max) C
Bulb Temperature	700 (max) C

• Product Dimensions

Overall Length C	80 (max) mm
Diameter D	20 (max) mm
Width F	23 (min), 23.5 (nom), 24 (max) mm
Light Center Length L	38 (min), 39 (nom), 40 (max) mm
Arc Length O	5.0 mm

• Product Data

Order code	928097905115
Full product code	928097905115
Full product name	MSR 200 HR
Order product name	MSR 200 HR 1CT/4
Pieces per pack	1
Packing configuration	4
Packs per outerbox	4
Bar code on pack - EAN1	8718696416044
Bar code on outerbox - EAN3	8718696416051
Logistic code(s) - 12NC	928097905115
Net weight per piece	22.000 gr

PHILIPS


MSR Hot Restrike

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and


remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Dimensional drawing




MSR 200 HR

Product	A (Min)	A (Norm)	A (Max)	C (Max)	D (Max)	D1 (Norm)	F (Min)	F (Norm)	F (Max)	L (Min)	L (Norm)	L (Max)	O (Norm)
MSR 200 HR	-	-	-	80	20	-	23	23.5	24	38	39	40	5.0




GZY9.5

Photometric data



MSR 125, 200, 250, 400, 575, 1200 (C), 2500, 4000, 6000, 12000, 18000 HR



MSR Hot Restrike



© 2015 Koninklijke Philips N.V. (Royal Philips)
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

www.philips.com/lighting

2015, September 27
data subject to change