


ENERGIZER L92-FR03

AAA



Industry Standard Dimensions




Specifications

Classification:	Lithium
Chemical System:	Lithium/Iron Disulfide (Li/FeS ₂)
Designation:	IEC-FR03
Nominal Voltage:	1.5 Volts
Storage Temp:	-40°C to 60°C
Operating Temp:	-40°C to 60°C
Typical Weight:	7.6 grams
Typical Volume:	3.8 cubic centimeters
Max Discharge:	1.5 amps continuous 2.0 amps pulse (2 sec on/8 sec off)
Max Rev Current:	2 uA
Typical Li Content:	0.5 grams
Shelf Life:	15 years at 21°C (90% of rated capacity)
Shipping:	For complete details, please reference: Global (except US): Special Provision A45 of the International Air Transport Association Dangerous Goods Regulations United States: 49 CFR 173.185

Milliamp-Hours Capacity

Constant Current Discharge to 0.9 Volts at 21°C




Milliwatt-Hours Capacity at Cold/Room Temperature

Constant Power Discharge to 1.0 Volts at 0°C and 21°C


Cold Temperature (0°C)

Constant Power Discharge



Room Temperature (21°C)

Constant Power Discharge



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER L92-FR03


AAA

Typical Discharge Curve Characteristics

Constant Current Discharge at 21°C (low and high drains)


Low Drain Performance

50mA Continuous (21°C)




High Drain Performance

600mA Continuous (21°C)




Constant Power Performance

Typical Characteristics to 1.0 Volts (21°C)



Constant Current Performance

Typical Characteristics to 1.0 Volts (21°C)




Industry Standard Tests (21°C)


REMOTE
24 ohm 15 sec/min 8 hrs/day




TAPE / ELECTRONIC GAME / DIGITAL AUDIO
100 mA 1 hr/day



PORTABLE LIGHTING
5.1 ohm LIF



PHOTOFLASH
600 mA 10 sec/min 1 hr/day



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.