ROLINE Multi-rate Media Converter Copper to Fiber 2.5/5/10 GbE Ethernet

21.13.1133


1. Product Overview

The media converter provides a great solution for connecting copper Ethernet and fiber Ethernet that supports multiple line rates of 10G/5G/2.5G/1Gbps capability. It is also equipped with Link Fault Pass-Through (LFPT) function. The LFPT function is useful for remote user when the link loss on one side of media converter can be passed to the other side, so that the near end can aware the fault condition that occurs at the far end behind two media converter connection.

2. Product Features

- The device supports the following multi-rate and media conversion:
 - 10GBASE-T to 10GBASE-R conversion
 - 5GBASE-T to 5GBASE-R conversion
 - 2.5GBASE-T to 2500BASE-X conversion
 - 1000BASE-T copper to 1000BASE-X (without auto-negotiation support) fiber conversion
- Supports auto-negotiation and Auto-MDI/MDI-X detection on the copper port
- Supports full wire speed conversion
- Supports transparent conversion for any packet types with no packet length limitation
- Provides link fault pass through function


3. Hardware Overview



Front panel



Rear panel



Right side

4. LED Indication

Standby stage:

LED	Color	Status	Operation
PWR	Green	ON	The converter is powered.
ACT	Green	Blink	Transmitting / Receiving data activities
		OFF	No data traffic
10G/5G Link	Blue	ON	10G or 5G connection rate
2.5G/1G Link	Green	ON	2.5G or 1G connection rate

Power on stage:

LFPT function	Operation
Enable	All LED except PWR LED are blinking twice
Disable	ALL LED are ON for 2 seconds

Alarm: All LED except PWR LED are blinking thrice when an unknown transceiver module is inserted.

5. Package Contents

The following items should be present in the product package:

- The media converter unit
- One power adapter

6. Technical Specifications

Specifications			
	IEEE 802.3, IEEE 802.3u, IEEE 802.3ab, IEEE 802.3z, IEEE 802.3an		
Chandand	Copper interface: 10GBASE-T, 5GBASE-T, 2.5GBASE-T, 1000BASE-T		
Standard	Fiber interface: 10GBASE-R(XFI), 5GBASE-R, 2500BASE-X,		
	1000BASE-X (without auto-negotiation support)		
	Copper port: Shielded RJ-45, Auto-negotiation, Auto-MDI/MDI-X,		
Network Ports	10G/5G/2.5G/1Gbps, Full/Half duplex		
Network Ports	Fiber port: SFP+ slot for SFP or SFP+ fiber transceiver,		
	10G/5G/2.5G/1Gbps, Full duplex		
	Copper port: Cat.6a, 7 or higher for 10GBASE-T up to 70m,		
Network Cables	Cat.5e or higher for 5G/2.5G/1000BASE-T up to 100m		
	Fiber port: MMF 50/125μm, 62.5/125μm, SMF 9/125μm		
DIP SW	Link Fault Pass Through function setting		
DIP 3W	DIP SW setting change will not take effect until next boot-up.		
	Rule 1: Fiber port is always forced to link down when copper port is down.		
	Rule 2: Fiber port link down forces copper port to link down when DIP SW		
LFPT function	(LFPT) is ON.		
	Note: Single fiber cable failure events are not supported by the LFPT		
	function.		
Power Input	+5VDC via external power adapter		
Power Consumption	3.8W max		
Housing	Enclosed metal with no fan		
Dimension	75 x 102 x 22.2 mm (WxDxH)		
Temperature	Operating: 0°C ~ 50°C, Storage: -20°C ~ 70°C		
Humidity	0% ~ 90% (non-condensing)		

The information contained in this document is subject to change without prior notice.Copyright © All Rights Reserved.