


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5055680671](#)  
**Status:** **Active**  
**Overview:** Micro-Lock Plus Wire-to-Board Connector System  
**Description:** Micro-Lock PLUS Vertical Header, 1.25mm Pitch, Single Row, Tin-Bismuth Plating, 6 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Packaging Specification 5055689200-200 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification 5055650000-000 (PDF)</a>	<a href="#">Product Literature (PDF)</a>
<a href="#">Application Specification AS-505565-002-001 (PDF)</a>	



**Agency Certification**

UL E29179

**General**

Product Family	PCB Headers
Series	<a href="#">505568</a>
Application	Signal, Wire-to-Board
Overview	<a href="#">Micro-Lock Plus Wire-to-Board Connector System</a>
Product Literature Order No	987651-4888
Product Name	Micro-Lock PLUS
UPC	889056511957

**Physical**

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	Polyamide
Net Weight	203.958/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Plating min - Mating	1.000µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-40°C to +105°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact 1.5A

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/30/2017 (7 July  
2017)

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[505568](#) Series

**Mates With**

[Micro-Lock PLUS Receptacle Housing 505565](#)

Voltage - Maximum

50V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Application Specification

AS-505565-002-001

Packaging Specification

5055689200-200

Product Specification

5055650000-000

Sales Drawing

5055680000-SD-000, 5055680001-SD-000

This document was generated on 11/15/2017

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**