

SDNC clamp holder for lathes, neutral

For longitudinal and copy turning using DC indexable inserts

ATORN[®]

Application

For longitudinal and copy turning using DC 55° indexable inserts



Version

- Precision-made steel support, bronzed, hardened, type D, pitch angle 62.5°, tip angle 55°, clearance angle 7°

Art. no.	17829 062
ISO name	SDNC N 16 16 X11-A
Shaft height	16 mm
Shank width	16 mm
Length	130 mm
Programming size	16 mm
Suitable for indexable inserts	DC.. 11T3..
Tool design	Neutral
DIN	4983

EAN-Code

4050293692914