

Worm Gear Units ZM/I

General data: Universal heavy-duty gearboxes.
4 sizes, centre distance 40, 50, 63 and 80 mm.
Centre distance 100 - 315 mm available on request.

Housing: High-quality grey cast iron, all sides machined and with mounting holes on 5 sides.

Gearing: 13 ratios from 5 to 83 : 1; worm shaft hardened and ground. Worm gear made from special centrifugally cast bronze.

Efficiency factor: The efficiency factors stated in the selection tables are guideline values for properly run-in and lubricated gearboxes at operating temperature with nominal load and driving worm shaft. Proper running in is a crucial factor influencing the lifetime of the gearbox. The starting efficiency factor (η_A) is, as the operating efficiency factor (h), depending on the lead angle.

Self-locking: Self-locking only occurs in worm gear units, when the unit cannot be driven from the output side. Worms with 4 and 6 threads sometimes permit transmission ratios for gearing up ($i = 5 : 1$ to $13.3 : 1$). If a gearbox must be implicitly self-locking, or must implicitly not be self-locking, we urge you to contact us.

The ratios 40:1 and 72:1 optimized for manual operation are static and dynamic self-locking.

Bearing system: All gearbox shafts with generously dimensioned roller bearings.

Lubrication: The gearboxes are lubricated for life using synthetic oil. Under normal operating conditions, no maintenance is required. The housing should be checked for leakages at an interval of approx. 2 years.

Ventilation: Size (centre distance) 40 is supplied without ventilation. With the other gearboxes, the sealing plug has to be exchanged with the separately packed venting filter.

Version A



Version HL



Venting Filter (VF)

| Size | A mm | B mm | C mm | D mm | E mm | F mm |
|------|---------|---------|---------|---------|---------|---------|
| 40* | - | - | - | - | - | - |
| 50 | 50 | 20 | 33 | 22 | 58 | 25 |
| 63 | 62,5 | 27,5 | 37 | 22 | 67 | 25 |
| 80 | 77,5 | 32,5 | 57 | 22 | 82 | 25 |


* Size 40 without Ventilation.

Lubrication Volume in Litre (dm³)

| Size | Mounting Position | | | |
|------|-------------------|------|-------|-------|
| | 1 | 2 | 3 + 4 | 5 + 6 |
| 40 | 0,20 | 0,25 | 0,20 | 0,20 |
| 50 | 0,30 | 0,60 | 0,45 | 0,45 |
| 63 | 0,50 | 1,10 | 0,70 | 0,80 |
| 80 | 0,90 | 2,10 | 1,40 | 1,60 |

The standard lubrication volume is calculated for mounting position 2. For other mounting positions and high permanent speeds it might have to be reduced, to avoid oil leakages.


Position of the Oil Fittings Size 50 - 80



Mounting Sides

The worm gear units can be mounted in any position and the shaft ends can be positioned to your requirements.

Sizes 40 - 80



Worm Gear Units ZM/I, Technical Data, Size 80

The input power $P_{1\text{permiss}}$ and output torques $T_{2\text{permiss}}$ listed in the selection tables are based on shock-free continuous operation, an operating time of 8 hours/day, 3 starts per hour, operating time (OT) = 100% and 20°C ambient temperature. The maximum output torques $T_{2\text{max}}$ may frequently be reached in short-term load peaks but they must not be exceeded. With an operating time under 90%, the permissible gearbox output can usually be increased.

i_n, i_{ist} = nominal ratio, real ratio.

n_1, n_2 [min⁻¹] = input speed, output speed.

$P_{1\text{perm}}$ [kW] = permissible input power.

$T_{2\text{perm}}$ [Nm] = permissible output torque (permanent).

$T_{2\text{max}}$ [Nm] = maximum output torque (peak).

η = operating efficiency.

Dimensions Table Page 907.


Version with foot mounting brackets or shafts on both sides on request.

| Version A Output Side 5 Product No. | Version A Output Side 6 Product No. | Version HL Hollow Shaft Product No. | Ratio i | n_1 min ⁻¹ | $n_2 \approx$ min ⁻¹ | $P_{1\text{perm}}$ KW | $T_{2\text{perm}}$ Nm | $T_{2\text{max}}$ Nm | η |
|---|---|---|------------------------------------|----------------------------|------------------------------------|--------------------------|--------------------------|-------------------------|--------|
| 421 031 00 | 421 031 01 | 421 033 00 | 5,0 : 1 | 1500 | 300 | 9,82 | 303 | 597 | 0,97 |
| | | | *30/6 | 1000 | 200 | 7,16 | 329 | 597 | 0,96 |
| | | | | 500 | 100 | 4,4 | 399 | 597 | 0,95 |
| | | | | 10 | 2 | 0,14 | 597 | 597 | 0,87 |
| 421 031 02 | 421 031 03 | 421 033 01 | 7,5 : 1 | 1500 | 200 | 7,22 | 330 | 681 | 0,96 |
| | | | *30/4 | 1000 | 133 | 5,35 | 364 | 681 | 0,95 |
| | | | | 500 | 67 | 3,31 | 441 | 681 | 0,93 |
| | | | | 10 | 1,3 | 0,11 | 681 | 681 | 0,84 |
| 421 031 04 | 421 031 05 | 421 033 02 | 10,0 : 1 | 1500 | 150 | 6,17 | 373 | 613 | 0,94 |
| | | | *40/4 | 1000 | 100 | 4,35 | 391 | 613 | 0,94 |
| | | | | 500 | 50 | 2,7 | 473 | 613 | 0,92 |
| | | | | 10 | 1 | 0,08 | 613 | 613 | 0,83 |
| 421 031 06 | 421 031 07 | 421 033 03 | 13,25 : 1 | 1500 | 113 | 2,4 | 188 | 335 | 0,93 |
| | | | *53/4 | 1000 | 75 | 1,69 | 197 | 335 | 0,92 |
| | | | | 500 | 38 | 0,93 | 212 | 335 | 0,89 |
| | | | | 10 | 0,75 | 0,03 | 335 | 335 | 0,83 |
| 421 031 08 | 421 031 09 | 421 033 04 | 15,0 : 1 | 1500 | 100 | 3,59 | 313 | 810 | 0,91 |
| | | | *30/2 | 1000 | 67 | 2,86 | 370 | 810 | 0,90 |
| | | | | 500 | 33 | 1,83 | 455 | 810 | 0,87 |
| | | | | 10 | 0,67 | 0,08 | 810 | 810 | 0,75 |
| 421 031 10 | 421 031 11 | 421 033 05 | 20,0 : 1 | 1500 | 75 | 3,11 | 356 | 725 | 0,90 |
| | | | *40/2 | 1000 | 50 | 2,46 | 416 | 725 | 0,89 |
| | | | | 500 | 25 | 1,59 | 518 | 725 | 0,85 |
| | | | | 10 | 0,5 | 0,05 | 725 | 725 | 0,74 |
| 421 031 12 | 421 031 13 | 421 033 06 | 26,5 : 1 | 1500 | 57 | 1,67 | 245 | 444 | 0,87 |
| | | | *53/2 | 1000 | 38 | 1,18 | 257 | 444 | 0,86 |
| | | | | 500 | 19 | 0,67 | 277 | 444 | 0,82 |
| | | | | 10 | 0,38 | 0,03 | 444 | 444 | 0,73 |
| 421 031 14 | 421 031 15 | 421 033 07 | 30,0 : 1 | 1500 | 50 | 1,92 | 308 | 878 | 0,84 |
| | | | *30/1 | 1000 | 33 | 1,55 | 364 | 878 | 0,82 |
| | | | | 500 | 17 | 1,03 | 454 | 878 | 0,77 |
| | | | | 10 | 0,33 | 0,04 | 878 | 878 | 0,60 |
| 421 031 16 | 421 031 17 | 421 033 08 | 40,0 : 1 | 1500 | 38 | 1,69 | 350 | 802 | 0,81 |
| | | | *40/1 | 1000 | 25 | 1,36 | 411 | 802 | 0,79 |
| | | | | 500 | 13 | 0,74 | 519 | 802 | 0,74 |
| | | | | 10 | 0,25 | 0,04 | 802 | 802 | 0,60 |
| - | - | 421 033 14 ¹⁾ | 43,0 : 1 | 1500 | 35 | 1,12 | 221 | 526 | 0,72 |
| | | | *43/1 optimized | 50 | 1,16 | 0,14 | 526 | 526 | 0,44 |
| | | | for manual operation ¹⁾ | | | | | | |
| 421 031 18 | 421 031 19 | 421 033 09 | 53,0 : 1 | 1500 | 28 | 1,04 | 271 | 501 | 0,78 |
| | | | *53/1 | 1000 | 19 | 0,75 | 285 | 501 | 0,75 |
| | | | | 500 | 9,4 | 0,43 | 309 | 501 | 0,70 |
| | | | | 10 | 0,19 | 0,02 | 501 | 501 | 0,59 |
| 421 031 20 | 421 031 21 | 421 033 10 | 62,0 : 1 | 1500 | 24 | 1,16 | 333 | 570 | 0,73 |
| | | | *62/1 | 1000 | 16 | 0,94 | 393 | 570 | 0,70 |
| | | | | 500 | 8,1 | 0,6 | 448 | 570 | 0,63 |
| | | | | 10 | 0,16 | 0,02 | 448 | 570 | 0,47 |
| 421 031 24 | 421 031 25 | 421 033 12 | 72,0 : 1 | 1500 | 21 | 1 | 314 | 498 | 0,69 |
| | | | *72/1 | 1000 | 14 | 0,82 | 370 | 498 | 0,66 |
| | | | | 500 | 6,9 | 0,46 | 370 | 498 | 0,58 |
| | | | | 10 | 0,14 | 0,02 | 370 | 498 | 0,41 |
| 421 031 26 ¹⁾ | 421 031 27 ¹⁾ | 421 033 13 ¹⁾ | 72,0 : 1 | 100 | 1,38 | 0,11 | 370 | 498 | 0,50 |
| | | | *72/1 optimized | 50 | 0,69 | 0,06 | 370 | 498 | 0,43 |
| | | | for manual operation ¹⁾ | | | | | | |
| 421 031 22 | 421 031 23 | 421 033 11 | 82,0 : 1 | 1500 | 18 | 0,84 | 304 | 510 | 0,69 |
| | | | *82/1 | 1000 | 12 | 0,59 | 304 | 510 | 0,66 |
| | | | | 500 | 6 | 0,33 | 304 | 510 | 0,60 |
| | | | | 10 | 0,12 | 0,01 | 304 | 510 | 0,47 |

* Example: Worm gear number of teeth 29 / worm shaft 6 threads.

¹⁾ This implicitly self-locking version is optimized for hand operation.

Dimensions Table Worm Gear Units ZM/I



The sides 1 to 6 are machined and can be used as mounting surfaces. The foot mounting brackets F can be connected to the sides 1 and 2. The sides 1, 2, 3, 5 and 6 are ex-works always supplied with threaded bores. If side 4 is to be used as mounting surface, the respective surface is supplied with threaded bores. The worm shaft end can be fitted on side 3 or 4 as desired. Shaft end with thread alignment according to DIN 332 sheet 2 see page 1055, feather keys and grooves according to DIN 6885/1. Position of the venting filter according to the table on page 902. The gearbox can function in any mounting position.

Version with foot mounting bracket or double-sided output shaft on request.

Gearbox Dimensions


| Size | ME | A | B | B ₁ | c | c ₁ | D ₄ | D x L | D ₁ x L ₁ | D ₂ | D ₃ | E | E ₁ | E ₂ * | E ₃ * | F ₁ |
|------|----|-----|-----|----------------|-----|----------------|----------------|---------|---------------------------------|----------------|----------------|-----|----------------|------------------|------------------|----------------|
| | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm |
| 40 | 40 | 104 | 90 | 85 | 125 | 110 | 70 | 14 x 24 | 22 x 36 | 22 | 35 | 70 | 70 | 55 | 35 | 53 |
| 50 | 50 | 140 | 105 | 100 | 150 | 130 | 90 | 16 x 28 | 25 x 42 | 25 | 40 | 80 | 100 | 70 | 50 | 65 |
| 63 | 63 | 164 | 120 | 115 | 165 | 145 | 110 | 18 x 28 | 30 x 58 | 30 | 45 | 95 | 125 | 87,5 | 62,5 | 80 |
| 80 | 80 | 204 | 140 | 135 | 190 | 165 | 140 | 24 x 36 | 38 x 58 | 38 | 55 | 115 | 155 | 107,5 | 77,5 | 100 |

| Size | f ₁ | f ₂ | G | G ₁ | H ₁ | h ₁ | H | I | k ₁ | O | O ₁ | S* | S ₁ | t ₁ | Weight |
|------|----------------|----------------|-----|----------------|----------------|----------------|-----|----|----------------|----|----------------|----------|----------------|----------------|--------|
| | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | mm | kg |
| 40 | 85 | 50 | 79 | 81 | 32 | 40 | 124 | 3 | 8 | 25 | 14 | M6 x 12 | 10 | 80 | 7 |
| 50 | 110 | 64 | 100 | 94,5 | 40 | 50 | 160 | 3 | 10 | 30 | 18 | M8 x 14 | 12 | 100 | 12 |
| 63 | 130 | 70 | 113 | 118 | 45 | 55 | 190 | 3 | 10 | 30 | 18 | M8 x 14 | 12 | 118 | 18 |
| 80 | 165 | 81 | 141 | 128 | 55 | 67 | 237 | 3 | 12 | 35 | 22 | M10 x 17 | 15 | 147 | 28 |

* Threaded bores on side 4 at extra charge. Dimensions may be subject to alteration.

Permissible Radial Loads F_R [N] for Normal Output Shaft and Bearing System

The perm. radial loads indicated in the table are calculated for the centre of the output shaft end, also calculating in the output speed and the nominal output torque. The values were calculated for the adverse rotational direction. The perm. radial loads only apply to unilateral load. If in your application high radial loads occur in combination with axial loads, we ask you to contact us.



| Size | Output Torques Nm | Permiss. Radial Load [N] at Output Speeds n ₂ [min ⁻¹] | | | | | | | | | | | | | | | | | |
|------|----------------------|---|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|------|
| | | 6 | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 | 80 | 100 | 125 | 160 | 200 | 250 | 320 |
| 40 | 0 - 80 | 2500 | 2375 | 2250 | 2125 | 2000 | 1875 | 1775 | 1675 | 1575 | 1400 | 1325 | 1250 | 1175 | 1125 | 1050 | 925 | 875 | 800 |
| | 125 - 160 | 3500 | 3325 | 3150 | 2970 | 2800 | 2620 | 2480 | 2340 | 2200 | 1960 | 1850 | 1750 | 1640 | 1570 | 1470 | 1290 | 1220 | 1120 |
| 63 | 0 - 200 | 5000 | 4750 | 4500 | 4250 | 4000 | 3750 | 3550 | 3350 | 3150 | 2800 | 2650 | 2500 | 2350 | 2250 | 2100 | 1850 | 1750 | 1600 |
| | 200 - 250 | 4600 | 4360 | 4140 | 3910 | 3680 | 3450 | 3260 | 3080 | 2900 | 2570 | 2440 | 2300 | 2160 | 2070 | 1930 | 1700 | 1610 | 1470 |
| | 250 - 320 | 3500 | 3325 | 3150 | 2975 | 2800 | 2625 | 2485 | 2345 | 2205 | 1960 | 1855 | 1750 | 1645 | 1575 | 1470 | 1295 | 1225 | 1120 |
| 80 | 0 - 500 | 7500 | 7120 | 6740 | 6370 | 6000 | 5620 | 5320 | 5000 | 4700 | 4200 | 4000 | 3750 | 3500 | 3370 | 3140 | 2770 | 2620 | 2400 |