

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**SECTION 1: Identification of the substance/mixture and of the company/undertaking**

- **1.1 Product identifier** 600342
- **Trade name:** Special Industrial Cleaner E-COLL
- **Article number:** 4317784464840
- **UFI:** H8H0-3NUY-580R-8G1T
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**
- **Sector of Use**  
SU21 Consumer uses: Private households / general public / consumers  
SU22 Professional uses: Public domain (administration, education, entertainment, services, craftsmen)
- **Application of the substance / the mixture** Cleaning material/ Detergent
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
E/D/E - Einkaufsbuero Deutscher Eisenhaendler GmbH  
EDE Platz 1  
D-42389 Wuppertal  
Germany  
  
Tel. +49 202 6096-0  
e-mail: sdb@ede.de
- **Further information obtainable from:** Product safety department
- **1.4 Emergency telephone number:** Giftinformationszentrum Mainz – Tel.: +49 (6131) 19240

**SECTION 2: Hazards identification**

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**

Aerosol 2	H223-H229	Flammable aerosol. Pressurised container: May burst if heated.
Skin Irrit. 2	H315	Causes skin irritation.
Eye Irrit. 2	H319	Causes serious eye irritation.
STOT SE 3	H336	May cause drowsiness or dizziness.
Asp. Tox. 1	H304	May be fatal if swallowed and enters airways.
Aquatic Chronic 3	H412	Harmful to aquatic life with long lasting effects.

**2.2 Label elements**

- **Labelling according to Regulation (EC) No 1272/2008**  
The product is classified and labelled according to the CLP regulation.

(Contd. on page 2)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 1)

**· Hazard pictograms**

GHS02 GHS07

**· Signal word** Warning**· Hazard-determining components of labelling:**

Hydrocarbons, C7-C9, isoalkanes  
propan-2-ol  
Naphtha (petroleum), hydrotreated heavy  
acetone

**· Hazard statements**

H223-H229 Flammable aerosol. Pressurised container: May burst if heated.  
H315 Causes skin irritation.  
H319 Causes serious eye irritation.  
H336 May cause drowsiness or dizziness.  
H412 Harmful to aquatic life with long lasting effects.

**· Precautionary statements**

P101 If medical advice is needed, have product container or label at hand.  
P102 Keep out of reach of children.  
P210 Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.  
P211 Do not spray on an open flame or other ignition source.  
P251 Do not pierce or burn, even after use.  
P260 Do not breathe spray.  
P271 Use only outdoors or in a well-ventilated area.  
P302+P352 IF ON SKIN: Wash with plenty of water.  
P304+P312 IF INHALED: Call a POISON CENTER/doctor if you feel unwell.  
P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.  
P332+P313 If skin irritation occurs: Get medical advice/attention.  
P362+P364 Take off contaminated clothing and wash it before reuse.  
P337+P313 If eye irritation persists: Get medical advice/attention.  
P410+P412 Protect from sunlight. Do not expose to temperatures exceeding 50 °C/122 °F.  
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

**· Additional information:**

EUH018 In use may form flammable/explosive vapour-air mixture.  
Product contains: Reportable explosives precursors. Making available, introduction, possession and use according to Regulation (EU) 2019/1148, Article 9.

**· 2.3 Other hazards****· Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**












(Contd. of page 2)

### SECTION 3: Composition/information on ingredients

#### 3.2 Mixtures

**Description:** Mixture of substances listed below with nonhazardous additions.

#### Dangerous components:

CAS: 67-63-0 EINECS: 200-661-7 Index number: 603-117-00-0 Reg.nr.: 01-2119457558-25-xxxx	propan-2-ol  Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336	25-50%
CAS: 67-64-1 EINECS: 200-662-2 Index number: 606-001-00-8 Reg.nr.: 01-2119471330-49-xxxx 01-2119498062-37-xxxx	acetone  Flam. Liq. 2, H225  Eye Irrit. 2, H319; STOT SE 3, H336 EUH066	20-25%
EC number: 921-728-3 Reg.nr.: 01-2119471305-42	Hydrocarbons, C7-C9, isoalkanes  Flam. Liq. 2, H225  Asp. Tox. 1, H304  Aquatic Chronic 2, H411  Skin Irrit. 2, H315; STOT SE 3, H336	20-25%
CAS: 124-38-9 EINECS: 204-696-9	carbon dioxide substance with a Community workplace exposure limit	3-5%
EC number: 927-241-2 Reg.nr.: 01-2119471843-32-XXXX	Naphtha (petroleum), hydrotreated heavy  Flam. Liq. 3, H226  Asp. Tox. 1, H304  STOT SE 3, H336 Aquatic Chronic 3, H412	3-5%

#### Regulation (EC) No 648/2004 on detergents / Labelling for contents

15 % or over but less than 30 %  
aliphatic hydrocarbons

**Additional information:** For the wording of the listed hazard phrases refer to section 16.

### SECTION 4: First aid measures

#### 4.1 Description of first aid measures

**General information:** Immediately remove any clothing soiled by the product.

#### After inhalation:

Supply fresh air.  
Seek medical treatment in case of complaints.

#### After skin contact:

Immediately wash with water and soap and rinse thoroughly.  
If skin irritation continues, consult a doctor.

**After eye contact:** Rinse opened eye for several minutes under running water. Then consult a doctor.

**After swallowing:** Do not induce vomiting; call for medical help immediately.

(Contd. on page 4)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 3)

- **4.2 Most important symptoms and effects, both acute and delayed**  
No further relevant information available.
- **4.3 Indication of any immediate medical attention and special treatment needed**  
No further relevant information available.

**SECTION 5: Firefighting measures**

- **5.1 Extinguishing media**
- **Suitable extinguishing agents:**  
CO<sub>2</sub>, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **For safety reasons unsuitable extinguishing agents:** Water with full jet
- **5.2 Special hazards arising from the substance or mixture** Can form explosive gas-air mixtures.
- **5.3 Advice for firefighters**
- **Additional information**  
Cool endangered receptacles with water spray.  
Collect contaminated fire fighting water separately. It must not enter the sewage system.

**SECTION 6: Accidental release measures**

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Wear protective equipment. Keep unprotected persons away.  
Ensure adequate ventilation
- **6.2 Environmental precautions:** No special measures required.
- **6.3 Methods and material for containment and cleaning up:**  
Ensure adequate ventilation.  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Do not flush with water or aqueous cleansing agents
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

**SECTION 7: Handling and storage**

- **7.1 Precautions for safe handling** Use only in well ventilated areas.
- **Information about fire - and explosion protection:**



Keep ignition sources away - Do not smoke.

Protect against electrostatic charges.

(Contd. on page 5)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 4)

Do not spray onto a naked flame or any incandescent material.  
Pressurised container: protect from sunlight and do not expose to temperatures exceeding 50°C, i.e. electric lights. Do not pierce or burn, even after use.

**· 7.2 Conditions for safe storage, including any incompatibilities****· Storage:****· Requirements to be met by storerooms and receptacles:**

Store in a cool location.

Observe official regulations on storing packagings with pressurised containers.

**· Information about storage in one common storage facility:** Store away from oxidising agents.**· Further information about storage conditions:** None.**· 7.3 Specific end use(s)** No further relevant information available.**SECTION 8: Exposure controls/personal protection****· 8.1 Control parameters****· Ingredients with limit values that require monitoring at the workplace:****CAS: 67-64-1 acetone**IOELV | Long-term value: 1210 mg/m<sup>3</sup>, 500 ppm**CAS: 124-38-9 carbon dioxide**IOELV | Long-term value: 9000 mg/m<sup>3</sup>, 5000 ppm**· DNELs****CAS: 67-63-0 propan-2-ol**

Inhalative	DNEL (worker)	500 mg/m <sup>3</sup> (Workers)
	DNEL (population)	89 mg/m <sup>3</sup> (cus)

**· Additional information:** The lists valid during the making were used as basis.**· 8.2 Exposure controls****· Appropriate engineering controls** No further data; see item 7.**· Individual protection measures, such as personal protective equipment****· General protective and hygienic measures:**

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes and skin.

**· Respiratory protection:**

Not necessary if room is well-ventilated.

Use suitable respiratory protective device in case of insufficient ventilation.

Self-contained respiratory protective device.

(Contd. on page 6)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 5)

**· Hand protection**

Protective gloves

**· Material of gloves**

Butyl rubber, BR

Recommended thickness of the material:  $\geq 0.4$  mm**· Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

**· Eye/face protection**

Tightly sealed goggles

**· Body protection: Protective work clothing****SECTION 9: Physical and chemical properties****· 9.1 Information on basic physical and chemical properties****· General Information**

· Colour:	Colourless
· Odour:	Characteristic
· Odour threshold:	Not determined.
· Melting point/freezing point:	Undetermined.
· Boiling point or initial boiling point and boiling range	56 °C
· Flammability	Not applicable.
· Lower and upper explosion limit	
· Lower:	0.7 Vol %
· Upper:	14.3 Vol %
· Flash point:	-17 °C
· Ignition temperature:	220 °C
· Decomposition temperature:	Not determined.
· pH	Not determined.
· Viscosity:	
· Kinematic viscosity	Not determined.
· Kinematic: 23 °C - 4 mm (ISO 2431)	
· Dynamic:	Not determined.
· Solubility	
· water:	Not miscible or difficult to mix.
· Partition coefficient n-octanol/water (log value)	Not determined.
· Vapour pressure:	Not determined.
· Density and/or relative density	
· Density at 20 °C:	0.76 g/cm <sup>3</sup>
· Relative density	Not determined.

(Contd. on page 7)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 6)

- Vapour density Not determined.
- **9.2 Other information**
- **Appearance:**
- **Form:** Aerosol
- **Important information on protection of health and environment, and on safety.**
- **Auto-ignition temperature:** Product is not selfigniting.
- **Explosive properties:** Not determined.
- **Change in condition**
- **Evaporation rate** Not applicable.
- **Information with regard to physical hazard classes**
- **Explosives** Void
- **Flammable gases** Void
- **Aerosols**  
Flammable aerosol. Pressurised container: May burst if heated.
- **Oxidising gases** Void
- **Gases under pressure** Void
- **Flammable liquids** Void
- **Flammable solids** Void
- **Self-reactive substances and mixtures** Void
- **Pyrophoric liquids** Void
- **Pyrophoric solids** Void
- **Self-heating substances and mixtures** Void
- **Substances and mixtures, which emit flammable gases in contact with water** Void
- **Oxidising liquids** Void
- **Oxidising solids** Void
- **Organic peroxides** Void
- **Corrosive to metals** Void
- **Desensitised explosives** Void

**SECTION 10: Stability and reactivity**

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

EU  
(Contd. on page 8)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 7)

**SECTION 11: Toxicological information****· 11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008****· Acute toxicity** Based on available data, the classification criteria are not met.**· LD/LC50 values relevant for classification:****CAS: 67-63-0 propan-2-ol**

Oral	LD50	5,045 mg/kg (rat)
Dermal	LD50	12,800 mg/kg (rabbit)
Inhalative	LC50/4h	30 ppm (rat)

**CAS: 67-64-1 acetone**

Oral	LD50	5,800 mg/kg (rat)
Dermal	LD50	20,000 mg/kg (rabbit)
Inhalative	LC50/4h	76 mg/m <sup>3</sup> (rat)

**Hydrocarbons, C7-C9, isoalkanes**

Oral	LD50	7,100-7,800 mg/kg (rat)
Dermal	LD50	2,200-2,500 mg/kg (rat)

**Naphtha (petroleum), hydrotreated heavy**

Oral	LD50	>15,000 mg/kg (rat)
Dermal	LD50	>5,000 mg/kg (rab)
Inhalative	LC50/4h	76 ppm (rat)

**· Skin corrosion/irritation**

Causes skin irritation.

**· Serious eye damage/irritation**

Causes serious eye irritation.

**· Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.**· Germ cell mutagenicity** Based on available data, the classification criteria are not met.**· Carcinogenicity** Based on available data, the classification criteria are not met.**· Reproductive toxicity** Based on available data, the classification criteria are not met.**· STOT-single exposure**

May cause drowsiness or dizziness.

**· STOT-repeated exposure** Based on available data, the classification criteria are not met.**· Aspiration hazard**

May be fatal if swallowed and enters airways.

**· 11.2 Information on other hazards****· Endocrine disrupting properties**

None of the ingredients is listed.



**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 8)

**SECTION 12: Ecological information****12.1 Toxicity****Aquatic toxicity:****CAS: 67-63-0 propan-2-ol**

EC50/24h &gt;10,000 mg/l (daphnia)

**CAS: 67-64-1 acetone**

LC50 (96h) 5,000 mg/L (Lepomis macrochirus)

LC50/48h 8,800 mg/l (Daphnia magna)

NOEC 430 mg/l (algae)

NOEC/16h 1,700 mg/l (Pseudomonas putida)

NOEC/48h 4,740 mg/l (Pseudokirchneriella subcapitata)

96h LC50 5,540 mg/l (Oncorhynchus mykiss)

**Hydrocarbons, C7-C9, isoalkanes**

LC50 21 mg/L /Dämpfe (rat)

**12.2 Persistence and degradability** No further relevant information available.**12.3 Bioaccumulative potential** No further relevant information available.**12.4 Mobility in soil** No further relevant information available.**12.5 Results of PBT and vPvB assessment****PBT:** Not applicable.**vPvB:** Not applicable.**12.6 Endocrine disrupting properties** For information on endocrine disrupting properties see section 11.**12.7 Other adverse effects****Remark:** Toxic for fish**Additional ecological information:****General notes:**

Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water

Toxic for aquatic organisms

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

Also poisonous for fish and plankton in water bodies.

**SECTION 13: Disposal considerations****13.1 Waste treatment methods:****European waste catalogue**

16 05 04\* gases in pressure containers (including halons) containing hazardous substances

EU

(Contd. on page 10)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 9)

**SECTION 14: Transport information**

- 14.1 UN number or ID number  
· ADR, IMDG, IATA UN1950
- 14.2 UN proper shipping name  
· ADR UN1950 AEROSOLS  
· IMDG AEROSOLS  
· IATA AEROSOLS, flammable

## · 14.3 Transport hazard class(es)

- ADR



- Class 2.5F Gases.
- Label 2.1

## · IMDG, IATA



- Class 2.1 Gases.
- Label 2.1

## · 14.4 Packing group

- ADR, IMDG, IATA Void

## · 14.5 Environmental hazards:

- Marine pollutant: Yes

## · 14.6 Special precautions for user

- Hazard identification number (Kemler code): -
- EMS Number: F-D,S-U
- Stowage Code SW1 Protected from sources of heat.  
SW22 For AEROSOLS with a maximum capacity of 1 litre: Category A. For AEROSOLS with a capacity above 1 litre: Category B. For WASTE AEROSOLS: Category C, Clear of living quarters.

(Contd. on page 11)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 10)

- **Segregation Code** SG69 For AEROSOLS with a maximum capacity of 1 litre:  
Segregation as for class 9. Stow "separated from" class 1 except for division 1.4.  
For AEROSOLS with a capacity above 1 litre:  
Segregation as for the appropriate subdivision of class 2.  
For WASTE AEROSOLS:  
Segregation as for the appropriate subdivision of class 2.
  
- **14.7 Maritime transport in bulk according to IMO instruments** Not applicable.

· **Transport/Additional information:**

- **ADR**
- **Limited quantities (LQ)** 1L
- **Excepted quantities (EQ)** Code: E0  
Not permitted as Excepted Quantity
- **Transport category** 2
- **Tunnel restriction code** D

- **IMDG**
- **Limited quantities (LQ)** 1L
- **Excepted quantities (EQ)** Code: E0  
Not permitted as Excepted Quantity
- **UN "Model Regulation":** UN 1950 AEROSOLS, 2.1

**SECTION 15: Regulatory information**

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** Methanol
- **Qualifying quantity (tonnes) for the application of lower-tier requirements** 200 t
- **Qualifying quantity (tonnes) for the application of upper-tier requirements** 500 t
- **REGULATION (EC) No 1907/2006 ANNEX XVII** Conditions of restriction: 3

**DIRECTIVE 2011/65/EU on the restriction of the use of certain hazardous substances in electrical and electronic equipment – Annex II**

None of the ingredients is listed.

- **Exposure scenario(s)**  
Exposure scenario(s) of ingredients (if present) are available on request at:  
sdb@ede.de

EU

(Contd. on page 12)

## Safety data sheet according to 1907/2006/EC, Article 31

Printing date 07.03.2022

Version number 303 (replaces version 302)

Revision: 07.03.2022

**Trade name: Special Industrial Cleaner E-COLL**

(Contd. of page 11)

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

#### · **Relevant phrases**

- H225 Highly flammable liquid and vapour.
- H226 Flammable liquid and vapour.
- H304 May be fatal if swallowed and enters airways.
- H315 Causes skin irritation.
- H319 Causes serious eye irritation.
- H336 May cause drowsiness or dizziness.
- H411 Toxic to aquatic life with long lasting effects.
- H412 Harmful to aquatic life with long lasting effects.
- EUH066 Repeated exposure may cause skin dryness or cracking.

#### · **Contact:** sdb@ede.de

#### · **Date of previous version:** 13.11.2020

#### · **Version number of previous version:** 302

#### · **Abbreviations and acronyms:**

ADR: Accord relatif au transport international des marchandises dangereuses par route (European Agreement Concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

vPvB: very Persistent and very Bioaccumulative

Aerosol 2: Aerosols – Category 2

Flam. Liq. 2: Flammable liquids – Category 2

Flam. Liq. 3: Flammable liquids – Category 3

Skin Irrit. 2: Skin corrosion/irritation – Category 2

Eye Irrit. 2: Serious eye damage/eye irritation – Category 2

STOT SE 3: Specific target organ toxicity (single exposure) – Category 3

Asp. Tox. 1: Aspiration hazard – Category 1

Aquatic Chronic 2: Hazardous to the aquatic environment - long-term aquatic hazard – Category 2

Aquatic Chronic 3: Hazardous to the aquatic environment - long-term aquatic hazard – Category 3

#### · \* **Data compared to the previous version altered.**