



SIRIUS SAFETY RELAY ADVANCED EXPANSION UNIT INPUT EXTENSION FOR ONE ADDITIONAL 2-CHANNEL OR TWO 1-CHANNEL SENSORS US = 24 V DC SPRING-LOADED CONNECTION

Figure similar

General technical data:		
product brand name		SIRIUS
Product designation		safety relays
Design of the product		Expansion unit
Protection class IP of the enclosure		IP20
Protection against electrical shock		finger-safe
Insulation voltage Rated value	V	50
Ambient temperature		
• during storage	°C	-40 ... +80
• during operation	°C	-25 ... +60
Air pressure acc. to SN 31205	kPa	90 ... 106
Relative humidity during operation	%	10 ... 95
Installation altitude at height above sea level maximum	m	2 000
Vibration resistance acc. to IEC 60068-2-6		5 ... 500 Hz: 0,75 mm
Shock resistance		10g / 11 ms
Surge voltage resistance Rated value	V	800
EMC emitted interference		IEC 60947-5-1, Class A
Installation environment regarding EMC		This product is suitable for Class A environments only. It can cause undesired radio-frequency interference in residential environments. If this is the case, the user must take appropriate measures.
Overvoltage category		Installation category III
Degree of pollution		3
Equipment marking acc. to DIN EN 61346-2		F
Number of sensor inputs 1-channel or 2-channel		1

Type of the safety-related wiring of the inputs		single-channel and two-channel
Product property cross-circuit-proof		Yes
Safety Integrity Level (SIL) acc. to IEC 61508		SIL3
Performance level (PL) acc. to EN ISO 13849-1		e
Category acc. to EN ISO 13849-1		4
PFHD with high demand rate acc. to EN 62061	1/h	0.000000001
Average probability of failure on demand (PFDavg) with low demand rate acc. to IEC 61508	1/y	0.000007
T1 value for proof test interval or service life acc. to IEC 61508	y	20
Hardware fault tolerance acc. to IEC 61508		1
Safety device type acc. to IEC 61508-2		Type B
Number of outputs as contact-affected switching element		
<ul style="list-style-type: none"> • as NC contact <ul style="list-style-type: none"> — for signaling function instantaneous contact — for signaling function delayed switching — safety-related instantaneous contact — safety-related delayed switching • as NO contact <ul style="list-style-type: none"> — for signaling function instantaneous contact — for signaling function delayed switching — safety-related instantaneous contact — safety-related delayed switching 		0 0 0 0 0 0 0 0
Stop category acc. to DIN EN 60204-1		0

General technical data:

Design of input Start input		Yes
Type of electrical connection Plug-in socket		No
Cable length between sensor and electronic evaluation device with Cu 1.5 mm ² and 150 nF/km maximum	m	4 000
Make time with automatic start		
<ul style="list-style-type: none"> • typical • for DC maximum 	ms ms	60 60
Make time with automatic start after power failure		
<ul style="list-style-type: none"> • typical • maximum 	ms ms	6 500 6 500
Make time with monitored start		
<ul style="list-style-type: none"> • maximum • typical 	ms ms	60 60

Backslide delay time after opening of the safety circuits typical	ms	40
Recovery time after opening of the safety circuits typical	ms	30
Pulse duration		
• of the sensor input minimum	ms	60
• of the ON pushbutton input minimum	s	0.15

Control circuit/ Control:

Type of voltage of the control supply voltage		DC
Control supply voltage		
• for DC		
— Rated value	V	24
Operating range factor control supply voltage rated value of the magnet coil		
• for DC		0.8 ... 1.2
Active power loss typical	W	1.2

Installation/ mounting/ dimensions:

mounting position		any
Required spacing for grounded parts at the side	mm	5
Required spacing with side-by-side mounting at the side	mm	0
Mounting type		screw and snap-on mounting
Width	mm	17.5
Height	mm	100
Depth	mm	121.6

Connections/ Terminals:

Type of electrical connection		spring-loaded terminals
Type of connectable conductor cross-section		
• solid		1x (0.5 ... 1.5 mm ²), 2x (0.5 ... 1.5 mm ²)
• finely stranded		
— with core end processing		1x (0.5 ... 1.0 mm ²), 2x (0.5 ... 1.0 mm ²)
— without core end processing		1x (0.5 ... 1.5 mm ²), 2x (0.5 ... 1.5 mm ²)
Type of connectable conductor cross-section for AWG conductors		
• solid		1x (20 ... 16), 2x (20 ... 16)
• stranded		1x (20 ... 16), 2x (20 ... 16)

Product Function:

Product function parameterizable		Sensor floating / sensor non-floating, monitored start / autostart, 1-channel / 2-channel sensor connection, cross-circuit detection, startup testing, antivalent sensors, 2-hand switches
Suitability for operation Device connector 3ZY12		Yes

Suitability for interaction press control		No
Suitability for use		
• safety switch		Yes
• Monitoring of floating sensors		Yes
• Monitoring of non-floating sensors		Yes
• magnetically operated switch monitoring		Yes
• safety-related circuits		Yes

Certificates/ approvals:

Certificate of suitability		
• TÜV (German technical inspectorate) certificate		Yes
• UL approval		Yes

General Product Approval	EMC	Functional Safety/Safety of Machinery	Declaration of Conformity
---------------------------------	------------	--	----------------------------------



[Type Examination](#)



Test Certificates	other
--------------------------	--------------

[Type Test Certificates/Test Report](#)

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator




<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3SK12202AB40>


Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3SK12202AB40/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3SK12202AB40&lang=en>





last modified:

09.03.2015