

MUSBR Series Rugged USB Connectors

Type A, Mini B, Mini AB

RUGGED USB CONNECTOR FOR HARSH ENVIRONMENT APPLICATION, GENERATION 2

Amphenol's MUSBR series USB Connectors serve many markets and applications across the globe including Automotive, Communications, Consumer, Data, Industrial and Medical.

MUSBR series is a line of Generation 2 ruggedized USB connectors with die cast housings and IP67 sealing, designed for Harsh Environment applications. MUSBR series provide reliable performance in extreme conditions for the most demanding applications, and mate with standard USB plugs.

- IP67 environmental sealing protects against water and dust
- Die cast metal housings protect against mechanical damage
- Compact design saves panel space
- Operating temperature range from -40°C to +105°C for extreme conditions
- RoHS compliant to meet environmental standards



FEATURES

- Internal and external seals made with flexible silicone rubber
- Die cast metal housings
- Improved thermal cycling performance
- Multiple options including USB 3.0, Type A, Mini B, Mini AB series
- Low profile shell design available for Type A series
- Similar in size compared to standard equivalents
- Wide variety of mounting and termination options
- RoHS compliant

BENEFITS

- Excellent sealing to IP67 and higher protection over wide temperature range
- Protects equipment from water and dust incursion
- Mechanically rugged and stable to protect against shock, vibration and impact
- Prevents distortion
- Suitable for outdoor application with wide operating temperature range
- Suitable for a wide variety of mating connectors which are readily available
- Compact design saves panel space
- Able to replace existing standard parts with little to no changes
- Replace virtually any existing standard connector using standard footprints and mounting hardware
- Meets environmental, health and safety requirements

TECHNICAL INFORMATION

MATERIAL

- External Shell: Die Cast Zinc, Nickel Plated
- Insulator Housing: High Temperature Resistant Engineering Thermoplastic, Glass Reinforced, UI 94V-0
- Panel Gasket: Conductive Silicone Rubber

MECHANICAL PERFORMANCE

- IP67
- UL: File E145615, Level DUXR2

ELECTRICAL PERFORMANCE

- Current Rating: Standard series A & B 1.5A max. per contact, Mini– 1.0A max. per contact
- Contact Resistance: Standard A- $30m\Omega$ max, Mini- $50m\Omega$ max
- Dielectric Withstanding Voltage: Standard A-500VAC rms, Mini-100 VAC rms

SPECIFICATION

Amphenol Product Specification: USB 2.0

ENVIRONMENTAL

- Temperature Life w/o Load: Per EIA-364-17, 105°C, 1000 Hours
- Thermal Shock: Per EIA-364-32, -40°C to +125°C, 5 Cycles
- Humidity: Per EIA 364–31, 10 Cycles, 240 Hrs,
 25°C to 65°C 90–95%RH, with -10°C Cold Shock
- Mixed Flowing Gas: Per EIA 364-65 Class IIA (Cl2, NO2, H2S & SO2), 14 Day Exposure
- Salt Spray: Per EIA 364-26, 250 Hours, 5% Salt, 35°C
- Solvent Resistance: Isopropyl Alcohol &
 5% Sodium Hydroxide Solution, 24 Hrs Each
- Solderability: Per EIA-364-52, 95% Coverage after Category 2 Steam Aging

APPROVALS AND CERTIFICATIONS

RoHS

PACKAGING

Box

TARGET MARKETS/APPLICATIONS



Car Navigation Systems Display Cluster Electric Vehicle



AC/DC pluggable power supplies Base Station Datacom Optical Transport Routers Switches Telecom



Home Entertainment Equipment Refrigerator



Data Center
External Portable Storage
High Density Ethernet switching
Router and Server
Storage System



Chemical Detection System
Industrial Control Equipment
Energy Meter
Gaming Machine
Lighting
Measuring Equipment
Parking Meter
POS Machine
Renewable Energy
Robotics
Smart Meter
Vending Machines



Analyzers Medical Diagnostics Ultrasound Equipment

► MUSBR Series Rugged USB Connectors

PART NUMBER SELECTOR

MU	SBR — X	Х	Х	Х	X	Х		Х				
USB 2.0 Receptacle							Unique S	pec	cial Code			
А	Standard A Series							No Digit		Standard part defin previous 10 digits	ned by	
В	Mini B Series							1 to 9		Unique special feat	ture	
Е	Mini AB Series					D	ust	Cover Opti	ons	;		
Termination Style		H			(0	Standard	(no	dust cover)			
1	Right Angle						1	With grey	col	lor dust cover (supp	lied bulk	packed)
2	Right Angle on PCB with Right Angle Cable					ļ	5	With blac	k co	olor dust cover (sup	plied bul	k packed)
2	Header	Cable		Shell & Thread Options								
	Right Angle on PCB with Right Angle			3 Standard Shell, Unified Thread								
3	Matching USB Ty			4	Low Profile Shell for Type A, Unified Thread							
	Connector		$\ \cdot \ $		5	Rea	Rear Flange Shell for Types B & AB, Unified Thread					d
4	Right Angle on PCB with Terminal Blocks				М	Standard Shell, Metric Thread						
5	Vertical			R	· · · · · · · · · · · · · · · · · · ·							
	Right Angle on PCB 3 with Vertical Cable Header				T Rear Flange Shell for Types B & AB, Metric Thread							
8				Colour								
		ght Angle on PCB		1 Black for Types A, B & E								
Α	with Holes for Wiring (Style 3 PCB)		Nı	Number of Contacts								
_	Right Angle on PCB		1 -	1 Standard 4 Contacts per Port for Types A								
В	with Vertical Sing Row Isolated Hea		5 Standard 5 Contacts per Port for Types B & AB									
Е	Right Angle on PO with Vertical Mat USB Type Connec	ching										