


PRODUCT DATA SHEET

Part Number: G650

Type	Size	Rating	Description
Incandescent	G11	24V 2.8W	G-3½ Edison screw lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
24	104	116	128	10.0	13.5	17.0	3,000

Notes:

- 1 **Base Type** E10/13 Nickel plated brass
- 2 **Filament Shape** C-2F
- 3 **Lamp Marking** CML 24V 2.8W
- 4 **Bead Colour** White or clear
- 5 **Environmental** RoHS & REACH SVHC compliant