

## RECORD ARKANSAS triangular files

Type 9020

**LAPPORT**  
SCHLEIFTECHNIK

### Application:

For machining of cutting tools, knives, instruments, engraving and clock-making tools, and similar

### Execution:

- For use with oil or petroleum
- Synthetic honing stones, manufactured according to a special ceramic process

### Delivery:

In cardboard box



<b>Art. no.</b>	<b>69436 020</b>
<b>Brand</b>	LAPPORT
<b>Manufacturer Part Number</b>	100348
<b>Length</b>	100 mm
<b>Surface structure</b>	Very fine
<b>Number of pieces per packet</b>	6 PCS
<b>Binding</b>	Ceramically bound
<b>Width</b>	10 mm
<b>Form</b>	Triangle
<b>Suitable for finishing</b>	1 - very suitable
<b>Suitable for main machining</b>	3 - less suitable
<b>Suitable for surface inspection</b>	1 - very suitable
<b>Suitable for surface care</b>	1 - very suitable
<b>Suitable for material rubber</b>	3 - less suitable
<b>Suitable for material cast iron</b>	3 - less suitable
<b>Suitable for material HSS</b>	1 - very suitable
<b>Suitable for material carbide</b>	3 - less suitable
<b>Suitable for material ceramic</b>	3 - less suitable
<b>Suitable for material plastics</b>	3 - less suitable
<b>Suitable for material non-ferrous metals</b>	3 - less suitable
<b>Suitable for material steel (hardened)</b>	1 - very suitable
<b>Suitable for material steel (unhardened)</b>	2 - suitable
<b>Suitable for material tool steel</b>	2 - suitable
<b>ISO</b>	525
<b>Length x width</b>	100 x 10 mm
<b>Type description</b>	RECORD-ARKANSAS
<b>Material of abrasive medium</b>	Fused aluminium oxide
<b>Gross Weight</b>	0.012 kg
<b>Product Group</b>	6HL