

Pneumatic straight grinder SRD 3-45/2

260 W



Application:

For spotting and reworking of moulds and tools.

Execution:

- With a long, thin tool spindle to enable work even in inaccessible places
- Rear air exhaust

Advantage:

- Handy ergonomics for effortless grinding
- The long, thin tool spindle allows the tool to be placed flat

Delivery:

Includes collet chuck ZG 5/3 mm and collet chuck key size 6 + 10; in box



Art. no.	75036 032
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150010775
Model	SRD 3-45/2
Valve design	Rotary valve
Motor design	Vane motor
Max. idle speed	45000 rpm
Power output	260 W
Air consumption	380 l/min
Length	196 mm
Diameter of housing	35 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Max. HM rotating milling cutter diameter	6 mm
Weight	0.31 kg
Made in	Germany
Compatible with	Hose unit 001366577
Gross Weight	1.350 kg
Product Group	748