

DATA SHEET

GENERAL PURPOSE CHIP RESISTORS

RC_L series

±0.1%, ±0.5%, ±1%, ±5% Sizes 0075/0100/0201/0402/0603/0805/ 1206/1210/1218/2010/2512

RoHS compliant & Halogen free







0075 to 2512

SCOPE

This specification describes RC series chip resistors with lead free terminations made by thick film process.

APPLICATIONS

• All general purpose application

FEATURES

- · Halogen Free Epoxy
- RoHS compliant
 - Products with lead free terminations meet RoHS requirements
 - Pb-glass contained in electrodes, resistors element and glass are exempted by RoHS
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Saving of PCB space
- None forbidden-materials used in products/production

ORDERING INFORMATION - GLOBAL PART NUMBER

Global part numbers are identified by the series, size, tolerance, packing type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

RC XXXX X X X XX XXXX L

(1) (2) (3) (4) (5)

6) (

(I) SIZE

0075/0100/0201/0402/0603/0805/1206/1210/1218/2010/2512

(2) TOLERANCE

 $B = \pm 0.1\%$

 $D = \pm 0.5\%$

 $F = \pm 1.0\%$

 $J = \pm 5.0\%$ (for jumper ordering, use code of J)

(3) PACKAGING TYPE

R = Paper taping reel

K = Embossed taping reel

S = ESD safe reel (0075/0100 only)

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

- = Based on spec.

(5) TAPING REEL & POWER

07 = 7 inch dia. Reel & Standard power

10 = 10 inch dia. Reel

13 = 13 inch dia, Reel

7W = 7 inch dia. Reel & 2 x standard power

7N = 7 inch dia. Reel, ESD safe reel (0075/0100 only)

3W = 13 inch dia. Reel & 2 x standard power

(6) RESISTANCE VALUE

There are 2~4 digits indicated the resistance value.

Letter R/K/M is decimal point

Example:

 $97R6 = 97.6\Omega$

 $9K76 = 9760\Omega$

 $IM = 1,000,000\Omega$

(7) DEFAULT CODE

Letter L is the system default code for ordering only. (Note)

ORDERING EXAMPLE

The ordering code for a RC0402 0.0625W chip resistor value $100 \text{K}\Omega$ with $\pm 5\%$ tolerance, supplied in 7-inch tape reel of 10,000 units per reel is: RC0402JR-07100KL.

NOTE

- I. All our RSMD products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process".
- 2. On customized label, "LFP" or specific symbol can be printed.



Chip Resistor Surface Mount

RC_L

SERIES

0075 to 2512

MARKING

RC0075 / RC0100 / RC0201 / RC0402




No Marking

...Fig. I

RC0603




1%, 0.5%,E24 exception values 10/11/13/15/20/75 of E24 series





1%, 0.5%, E96 refer to EIA-96 marking method, including values 10/11/13/15/20/75 of E24 series





5%, E24 series: 3 digits


First two digits for significant figure and 3rd digit for number of zeros

RC0805 / RC1206 / RC1210 / RC2010 / RC2512



1%, 0.5%, E24/E96 series : 4 digits


First three digits for significant figure and 4th digit for number of zeros



5%, E24 series: 3 digits


First two digits for significant figure and 3rd digit for number of zeros

RC1218



E-24 series: 3 digits, ±5%

First two digits for significant figure and 3rd digit for number of zeros



Both E-24 and E-96 series: 4 digits, ±1% & ±0.5%

First three digits for significant figure and 4th digit for number of zeros


For further marking information, please see special data sheet "Chip resistors marking".

0075 to 2512

CONSTRUCTION

The resistor is constructed on top of a high-grade ceramic body. Internal metal electrodes are added on each end to make the contacts to the thick film resistive element. The composition of the resistive element is a noble metal imbedded into a glass and covered by a second glass to prevent environmental influences. The resistor is laser trimmed to the rated resistance value. The resistor is covered with a protective epoxy coat, finally the two external terminations (matte tin on Ni-barrier) are added, as shown in Fig. 9.

Outlines



DIMENSION

Table I

I					
TYPE	L (mm)	W (mm)	H (mm)	I _I (mm)	l ₂ (mm)
RC0075	0.30±0.01	0.15±0.01	0.13±0.01	0.08±0.03	0.08±0.03
RC0100	0.40±0.02	0.20±0.02	0.13±0.02	0.10±0.03	0.10±0.03
RC0201	0.60±0.03	0.30±0.03	0.23±0.03	0.10±0.05	0.15±0.05
RC0402	1.00±0.05	0.50±0.05	0.35±0.05	0.20±0.10	0.25±0.10
RC0603	1.60±0.10	0.80±0.10	0.45±0.10	0.25±0.15	0.25±0.15
RC0805	2.00±0.10	1.25±0.10	0.50±0.10	0.35±0.20	0.35±0.20
RC1206	3.10±0.10	1.60±0.10	0.55±0.10	0.45±0.20	0.45±0.20
RC1210	3.10±0.10	2.60±0.15	0.55±0.10	0.45±0.15	0.50±0.20
RC1218	3.10±0.10	4.60±0.10	0.55±0.10	0.45±0.20	0.40±0.20
RC2010	5.00±0.10	2.50±0.15	0.55±0.10	0.60±0.20	0.55±0.20
RC2512	6.35±0.10	3.10±0.15	0.55±0.10	0.60±0.20	0.60±0.20

ELECTRICAL CHARACTERISTICS

Table 2

CHARAC- TERISTICS	POWER	OPERATING TEMPERATURE RANGE	MAXIMUM WORKING VOLTAGE	MAXIMUM OVERLOAD VOLTAGE	DIELECTRIC WITHSTANDING VOLTAGE	RESISTANCE RANGE	TEMPERATURE COEFFICIENT	JUMPER CRITERIA
RC0075	1/50 W	-55°C to 125°C	10V	25V	25V	5% (E24) 10Ω≦R≦1MΩ 1% (E24/E96) 10Ω≦R≦1MΩ Jumper<50mΩ	10Ω≦R<100Ω -200~+600ppm°C 100Ω≦R≦1MΩ ±200ppm°C	Rated Current 0.5A Maximum Current 1.0A
RC0100	1/32 W	-55°C to 125°C	157	30V	30V	5% (E24) 1Ω≦R≦22MΩ 1% (E24/E96) 1Ω≦R≦10MΩ 0.5% (E24/E96) 33Ω≦R≦470KΩ Jumper<50mΩ	$I\Omega$ ≦R< $I\Omega\Omega$ -200~+600ppm°C $I0\Omega$ ≤ R < $I00\Omega$: ±300ppm/°C $I00\Omega$ ≤ R ≤ $I0M\Omega$: ±200ppm/°C $I0M\Omega$ < R ≤ $I0M\Omega$: ±250ppm/°C	Rated Current 0.5A Maximum Current I.0A

Product specification

5

	Га	h	۱۸	7
- 1	ıα	U	ıe	_

Table 2								
CHARAC- TERISTICS	POWER	OPERATING TEMPERATURE RANGE	MAXIMUM WORKING VOLTAGE	MAXIMUM OVERLOAD VOLTAGE	DIELECTRIC WITHSTANDING VOLTAGE	resistance Range	TEMPERATURE COEFFICIENT	JUMPER CRITERIA
RC0201	1/20 W	-55°C to 125°C	25V	50V	50V	5% (E24) IΩ≦R≦I0MΩ I% (E24/E96) IΩ≦R≦I0MΩ 0.5% (E24/E96) IΩ≦R≦IMΩ 0.1% (E24/E96) I0Ω≦R≦IMΩ Jumper<50mΩ	IΩ≦R≦I0Ω -100~+350ppm°C I0Ω <r≦i0mω ±200ppm°C</r≦i0mω 	Rated Current 0.5A Maximum Current 1.0A
RC0402	1/16 W	-55°C to 155°C	50V	100V	100V	5% (E24) IΩ≦R≦22MΩ I% (E24/E96) IΩ≦R≦10MΩ 0.5% (E24/E96) IΩ≦R≦IMΩ 0.1% (E24/E96) I0Ω≦R≦IMΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±I00ppm°C I0MΩ<r≦22mω ±200ppm°C</r≦22mω </r≦i0mω 	Rated Current I.0A Maximum Current 2.0A
	I/8W	-55°C to 155°C	50V	100∨	100V	5% (E24) IΩ≦R≦IMΩ I% (E24/E96) IΩ≦R≦IMΩ	IΩ≦R≦IMΩ ±200ppm°C	
RC0603	1/10 W	-55°C to 155°C	75 V	150V	150V	5% (E24) IΩ≦R≦22MΩ I% (E24/E96) IΩ≦R≦10MΩ 0.5% (E24/E96) IΩ≦R≦IMΩ 0.1% (E24/E96) I0Ω≦R≦IMΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±I00ppm°C I0MΩ<r≦22mω ±200ppm°C</r≦22mω </r≦i0mω 	Rated Current I.0A Maximum Current 2.0A
	1/5 W	-55°C to 155°C	75V	150V	150V	5% (E24) IΩ≦R≦IMΩ I% (E24/E96) IΩ≦R≦IMΩ	IΩ≦R≦IMΩ ±200ppm°C	
RC0805	1/8 W	-55°C to 155°C	150V	300V	300V	5% (E24) IΩ≦R≦I00MΩ I% (E24/E96) IΩ≦R≦I0MΩ 0.5% (E24/E96) IΩ≦R≦IMΩ 0.1% (E24/E96) I0Ω≦R≦IMΩ 10Ω≦R≦IMΩ 10%, 20% (E24) 24MΩ≦R≦I00MΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±I00ppm°C I0MΩ<r≦22mω ±200ppm°C 24MΩ<r≦i00mω ±300ppm°C</r≦i00mω </r≦22mω </r≦i0mω 	Rated Current 2.0A Maximum Current 5.0A
	1/4 W	-55℃ to 155℃	150V	300V	300V	5% (E24) ΙΩ≦R≦ΙΜΩ Ι% (E24/E96) ΙΩ≦R≦ΙΜΩ	IΩ≦R≦IMΩ ±200ppm°C	

Chip Resistor Surface Mount RC_L SERIES 0075 to 2512

FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please refer to data sheet "Chip resistors mounting"

_	_			_
	la	b	le	2

CHARAC- TERISTICS	POWER	OPERATING TEMPERATURE RANGE	MAXIMUM WORKING VOLTAGE	MAXIMUM OVERLOAD VOLTAGE	DIELECTRIC WITHSTANDING VOLTAGE	resistance range	TEMPERATURE COEFFICIENT	JUMPER CRITERIA
RC1206	1/4 W	-55°C to 155°C	200V	400V	500V	5% (E24) 1Ω≦R≦100MΩ 1% (E24/E96) 1Ω≦R≦10MΩ 0.5% (E24/E96) 1Ω≦R≦1MΩ 0.1% (E24/E96) 10Ω≦R≦1MΩ 10%, 20% (E24) 24MΩ≦R≦100MΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±I00ppm°C I0MΩ<r≦22mω ±200ppm°C 24MΩ≦R≦I00MΩ ±300ppm°C</r≦22mω </r≦i0mω 	Rated Current 2.0A Maximum Current 10.0A
	1/2 W	-55°C to 155°C	200V	400V	500V	5% (E24) IΩ≦R≦IMΩ I% (E24/E96) IΩ≦R≦IMΩ	IΩ≦R≦IMΩ ±200ppm°C	
RC1210	1/2 W	-55°C to 155°C	200V	500V	500V	5% (E24) IΩ≦R≦22MΩ I% (E24/E96) IΩ≦R≦10MΩ 0.1%, 0.5% (E24/E96) I0Ω≦R≦IMΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±100ppm°C I0MΩ<r≦22mω ±200ppm°C</r≦22mω </r≦i0mω 	Rated Current 2.0A Maximum Current 10.0A
RC1218	ΙW	-55°C to 155°C	200V	500V	500V	5% (E24) IΩ≦R≦IMΩ I% (E24/E96) IΩ≦R≦IMΩ 0.1%, 0.5% (E24/E96) I0Ω≦R≦IMΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦imω ±100ppm°C</r≦imω 	Rated Current 6.0A Maximum Current 10.0A
RC2010	3/4 W	-55°C to 155°C	200V	500V	500V	5% (E24) IΩ≦R≦22MΩ I% (E24/E96) IΩ≦R≦10MΩ 0.1%, 0.5% (E24/E96) I0Ω≦R≦1MΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±I00ppm°C I0MΩ<r≦22mω ±200ppm°C</r≦22mω </r≦i0mω 	Rated Current 2.0A Maximum Current 10.0A
RC2512	ΙW	-55°C to 155°C	200V	500V	500V	5% (E24) IΩ≦R≦22MΩ I% (E24/E96) IΩ≦R≦10MΩ 0.1%, 0.5% (E24/E96) I0Ω≦R≦IMΩ Jumper<50mΩ	IΩ≦R≦I0Ω ±200ppm°C I0Ω <r≦i0mω ±I00ppm°C I0MΩ<r≦22mω ±200ppm°C</r≦22mω </r≦i0mω 	Rated Current 2.0A Maximum Current 10.0A
	2 W	-55°C to 155°C	200V	400V	500V	5% (E24) ΙΩ≦R≦ΙΜΩ Ι% (E24/E96) ΙΩ≦R≦ΙΜΩ	IΩ≦R≦IMΩ ±200ppm°C	

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PACKING STYLE	PAPER TAPINO	G REEL (R)		ESD SAFE REEL (S) (4MM WIDTH, IMM PITCH PLASTIC EMBOSSED)	EMBOSSED TAPING REEL
REEL DIMENSION	7" (178 mm)	10" (254mm)	13" (330 mm)	7" (178 mm)	7" (178 mm)
RC0075				20000	
RC0100	20000		80000	40000	
RC0201	10000	20000	50000		
RC0402	10000	20000	50000		
RC0603	5000	10000	20000		
RC0805	5000	10000	20000		
RC1206	5000	10000	20000		
RC1210	5000	10000	20000		
RC1218					4000
RC2010					4000
RC2512					4000

NOTE

YAGEO

For tape and reel specification/dimensions, please refer to data sheet "Chip resistors packing".

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

RC0402 to RC2512 Range: -55°C to +155°C (Fig. 10-1) RC0075 to RC0201 Range: -55°C to +125°C (Fig. 10-2)

POWER RATING

Each type rated power at 70 °C:

RC0075=1/50W

RC0100=1/32W

RC0201=1/20W

RC0402=1/16W, 1/8W

RC0603=1/10W, 1/5W

RC0805=1/8W, 1/4W

RC1206=1/4W, 1/2W

RC1210=1/2W

RC1218=1W

RC2010=3/4W

RC2512=1W, 2W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(PxR)}$$


or max. working voltage whichever is less


Where

V = Continuous rated DC or AC (rms) working voltage (V)

P = Rated power (W)

 $R = Resistance value (\Omega)$







SERIES 0075 to 2512

TESTS AND REQUIREMENTS

Table 8 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Temperature Coefficient of Resistance	MIL-STD-202 Method 304	At +25/–55°C and +25/+125°C	Refer to table 2
(T.C.R.)		Formula:	
		T.C.R= $\frac{R_2 - R_I}{R_I(t_2 - t_I)} \times I0^6 \text{ (ppm/°C)}$	
		Where	
		t_1 =+25 ° C or specified room temperature	
		t_2 =-55 °C or +125 °C test temperature	
		R_1 =resistance at reference temperature in ohms R_2 =resistance at test temperature in ohms	
Life/ Endurance	MIL-STD-202 Method 108A IEC 60115-1 4.25.1	At 70±2°C for 1,000 hours; RCWV applied for 1.5 hours on and 0.5 hour off, still air required	$0075: \pm (5\% + 100 \text{m}\Omega)$ $< 100 \text{m}\Omega \text{ for jumper}$ $01005: \pm (3\% + 50 \text{m}\Omega)$ $< 100 \text{m}\Omega \text{f or jumper}$ $Others:$ $\pm (1\% + 50 \text{m}\Omega) \text{ for B/D/F tol}$ $\pm (3\% + 50 \text{m}\Omega) \text{ for J tol}$ $< 100 \text{mR for jumper}$
High Temperature Exposure	MIL-STD-202 Method 108A IEC 60068-2-2	I,000 hours at maximum operating temperature depending on specification, unpowered.	0075: \pm (5%+100m Ω) <100m Ω for jumper 01005: \pm (1% +50m Ω) < 50m Ω f or jumper Others:
			$\pm (1\% + 50 \text{m}\Omega)$ for B/D/F tol $\pm (2\% + 50 \text{m}\Omega)$ for J tol
			<50mR for jumper
Moisture Resistance	MIL-STD-202 Method 106G	Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d with 25°C / 65°C 95% R.H, without steps	0075: \pm (2%+100mΩ) <100mΩ for jumper 01005: \pm (2% +50mΩ) < 100mΩf or jumper
		7a & 7b, unpowered Parts mounted on test-boards, without	Others:
		condensation on parts	$\pm (0.5\% + 50 \text{m}\Omega)$ for B/ D/F tol
		'	$\pm (2\% + 50 \text{m}\Omega)$ for J tol < 100mR for jumper
Humidity	IEC 60115-1 4.24.2	Steady state for 1000 hours at 40°C / 95% R.H. RCWV applied for 1.5 hours on and 0.5 hour off	0075: \pm (5%+100m Ω) no visible damage 01005: \pm (3% +50m Ω) $<$ 100m Ω f or jumper
			Others: $ \pm (1\% + 50 \text{m}\Omega) \text{ for B/D/F tol} $ $ \pm (2\% + 50 \text{m}\Omega) \text{ for J tol} $ $ < 100 \text{mR for jumper} $



Chip Resistor Surface Mount RC_L SERIES 0075 to 2512

Thermal	MIL-STD-202 Method 107G	-55/+125°C	$0075/01005: \pm (1\% + 50 \text{m}\Omega)$	
Shock		Note Number of cycles required is 300.	$<$ 50m Ω f or jumper Others:	
		Devices mounted	$\pm (0.5\% + 50 \text{m}\Omega)$ for B/D/F tol	
		Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air - Air	$\pm (1\% + 50 \text{m}\Omega)$ for tol	
		Dwell time is 13 minutes, Air - Air	< 50mR for jumper	
Short Time Overload	IEC 60115-1 4.13	2.5 times RCWV or maximum overload voltage which is less for 5 seconds at room temperature	0075/01005: \pm (2% +50mΩ) < 50mΩf or jumper	
			Others:	
			$\pm (1\% + 50 \text{m}\Omega)$ for B/D/F tol	
			$\pm (2\% + 50 \text{m}\Omega)$ for J tol	
			<50mR for jumper	
			No visible damage	
Board Flex/ Bending	IEC 60115-1 4.33	Device mounted or as described only I board bending required	0075/01005: \pm (1% +50mΩ) < 50mΩf or jumper	
		bending time: 60±5 seconds	Others:	
		0075/0100/0201/0402:5mm;	$\pm (1\% + 50 \text{m}\Omega)$ for B/D/F/J tol	
		0603/0805:3mm;	<50mR for jumper	
		1206 and above:2mm	No visible damage	
Solderability	J-STD-002 test B	Electrical Test not required Magnification 50X	W ell tinned	
- Wetting		SMD conditions:	(>95% covered)	
		Ist step: method B, aging 4 hours at I55°C dry heat	No visible damage	
		2nd step: leadfree solder bath at 245±3°C Dipping time: 3±0.5 seconds		
-Leaching	J-STD-002 test D	Leadfree solder ,260°C, 30 seconds immersion time	No visible damage	
-Resistance to	MIL-STD-202 Method 210F	Condition B, no pre-heat of samples	0075: ± (3%+50mΩ)	
Soldering Heat	IEC 60115-1 4.18	Leadfree solder, 260°C ± 5 °C, 10 ± 1 seconds immersion time	$<$ 50m Ω for jumper 01005: \pm (1% +50m Ω) $<$ 50m Ω f or jumper	
		Procedure 2 for SMD: devices fluxed and	Others:	
		cleaned with isopropanol	\pm (0.5% +50m Ω) for B/D/F tol. \pm (1% +50m Ω) for J tol. <50mR for jumper	
			No visible damage	

Chip Resistor Surface Mount RC_L

SERIES

REVISION HISTORY

REVISION	DATE	CHANGE NOTIFICATION	DESCRIPTION
Version 12	Aug. 02, 2022	-	- 12 dimension updated, for size 1206, size 2010, size 2512.
Version 11	May 15, 2020	-	- Extend RC0201, RC0402, RC0603, RC0805, RC1206 D tol resistance range to lohm
Version 10	Dec. 12, 2018	-	- Updated 0075 dimensions
Version 9	Mar. 06, 2018	-	- Add 0.5%/1% marking rule for RC0603 ~ RC2512 based on marking datasheet
Version 8	July 10, 2017	-	- Add "3W" part number coding for 13" Reel & double power
Version 7	Mar. 7, 2017	-	- Add 10" packing
Version 6	Feb.15, 2017	-	- Extend RC0805 and RC1206 resistance range to 100Mohm
Version 5	Oct. 06, 2016	-	- Description: Update Dimension of I2 of RC2512 (2W)
Version 4	Jan. 22, 2016	-	- Update resistance range
Version 3	Dec. 24, 2015	-	- Updated test and requirements
Version 2	Jul. 23, 2015	-	- Updated test and requirements
Version I	Jan. 21, 2015	-	- ESD Safe Reel update
Version 0	Dec. 15, 2014	-	- First issue of this specification

 $[\]label{thm:content} \begin{tabular}{ll} ``YAGEO'' reserves' all the rights' for revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of this datasheet without further notification, as long as the products itself are unchanged. \\ \begin{tabular}{ll} ``YAGEO''' revising the content of the product of the$ Any product change will be announced by PCN."