

**Industrial Ethernet
IE-C5DD4UG0200MSSXXX-X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



Industrial Ethernet connection technology by Weidmüller offers the optimal solution for the infrastructure of your machine, system or factory. All connection technology is available from one source.

The benefits for you:

- IEC-standardised connectors, in the variants 1, 4, 5 , 6 and 14
- Cat. 6 throughout_A with **STEADYTEC**® technology
- pre-assembled cables and cables sold by the metre
- Copper and fibre-optic cables
- in IP20 and IP67
- all relevant industrial connections: RJ45, M12, SC, ...
- comprehensive range of accessories

General ordering data

Type	IE-C5DD4UG0200MSSXXX-X
Order No.	1111440200
Version	Dragline cable, PROFINET, M12 D-code – IP 67 straight socket, Open, Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B), PUR, 20 m
GTIN (EAN)	4050118485769
Qty.	1 pc(s).

**Industrial Ethernet
IE-C5DD4UG0200MSSXXX-X**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Technical data
Dimensions and weights

Length	20 m	Length (inches)	0.787 inch
Net weight	1,240 g	Insulation cross-section	1.5 mm

Temperatures

Operating temperature, max.	70 °C	Operating temperature, min.	-40 °C
Storage temperature, max.	70 °C	Storage temperature, min.	-50 °C
Operating temperature	-40 °C...70 °C	Storage temperature	-50 °C...70 °C
Installation temperature	-20 °C...60 °C		

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1
------------	----------------

Electrical properties

Insulation strength	500,000 Ω
---------------------	-----------

Standards

Standard, insulating material	DIN EN 50290-2-23 (VDE 0819) Table 2/A (HD 624.3)	Standard, wire material	DIN EN 13602 Cu-ETP-A
Standard, shielding material	DIN EN 13602 Cu-ETP-A..B	Certificate no. (cULus)	E316369

Cable structure

Wire material	Stranded tin-plated copper wire	Standard designations	2YH(ST)C11Y 2x2x0,75/1,5-100 LI VZN GN FRNC
Strands	7	Cross-section	4*AWG 22/7 - 0.36 mm ²
Insulation	PE	Insulation cross-section	1.5 mm
Wire core insulation thickness	0.38 mm	No. of wires	4
Arrangement of wire cores	Star-quad	Colour sequence or wires - wire pairs	white, yellow, blue, orange
Diameter of inner sheathing	3.9 mm	Filler	As central element
Shielding	SF/UTP	Complete shielding	Aluminium foil, Shielding braid made from copper wiring
Shielding braid thickness	0.13 mm	Overlap of shielding braid	85 %
Material sheath	PUR	Sheath diameter, min.	6.3 mm
Sheath diameter, max.	6.7 mm	Sheathing material thickness	0.9 mm
Sheathing colour	green (RAL 6018)		

Electrical properties of cable

Category	Cat.5 (ISO/IEC 11801) / Cat.5e (TIA T568-B)	Operating voltage (UL rating)	600 V undefined
Test voltage: wire-wire-shield	2000 V _{eff} , 50 Hz, 1 min	Characteristic impedance	100 ± 15 Ω at 1-100 MHz
Loop resistance	120 Ω/km	Deviation	40 ns/100m
Resistance differential	3 %	Transfer impedance	20 mΩ/m at 10 MHz
Insulation strength	500,000 Ω	Capacity at 1 kHz	52 nF/km
Signal propagation time	5.3 ns/m	Speed	180 m/min

Creation date May 27, 2019 3:27:58 PM CEST

Industrial Ethernet
IE-C5DD4UG0200MSSXXX-X

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data
Mechanical and material properties of cable

Bending cycles	3 Mio	Min. bending radius, once only	5 x cable diameter
Min. bending radius, repetitive	7.5 x cable diameter	Pulling force	≤ 150 N
Speed	180 m/min	Acceleration	4 m/s ²
Abrasion resistance	very good	Resistance to spread of flame	in accordance with IEC 60332-1
Resistance to oils	in accordance with IEC 60811-2-1	UV-resistant	Yes
Silicone-free	Yes	Halogen	halogen-free, according to IEC 60754-2
Fire propagation	No		

plug

Connector left	M12 D-code – IP 67 straight socket	Connector right	Open
----------------	------------------------------------	-----------------	------

Classifications

ETIM 5.0	EC000830	ETIM 6.0	EC002599
eClass 6.2	27-06-03-90	eClass 7.1	27-06-03-90
eClass 8.1	27-06-03-90	eClass 9.0	27-06-03-08
eClass 9.1	27-06-03-08		

Approvals

Approvals



ROHS Conform

Downloads

Brochure/Catalogue	FL FIELDWIRING EN PI PROFINET CABLING EN
Engineering Data	EPLAN, WSCAD
User Documentation	MAN IE GUIDE DE MAN IE GUIDE EN