

ER collet chuck with flat face

ISO 7388-1

ATORN[®]

Application

For clamping tools with lateral driving surfaces in accordance with DIN 1835 B and DIN 6535 HB

Version

- Pre-balanced G6.3/25,000 rpm
- Precision design
- Polished external and internal cones
- High concentricity

Advantage

- Increased rigidity and vibration damping due to positive-locking flat face
- Extends the service life of cutting tools



Art. No.	23296 462
Tool holding device	SK 40
Form	AD
Collet type	ER 32 (470 E)
Projecting length	100 mm
Outer diameter	50 mm
Min./max. clamping range	2-20 mm
Coolant supply	Yes
Balancing quality	G 6,3 at 25000 rpm
Concentricity tolerance	5 µm

EAN-Code

4050293647235