

Inside micrometer

Micromar 44F



Application:

For measuring bore diameters, distances on workpieces etc.

Execution:

- Scale with anti-glare, brushed chromium plated finish
- Lightweight, kink-resistant tube design
- Measuring spindle completely hardened and ground

Delivery:

In a case



Art. no.	31680 070
Brand	MAHR
Manufacturer Part Number	4163003
Min./max. length measuring range	70-100 mm
Error limit	5 µm
Vernier scale	0.01 mm
Measuring spindle increments	0.5 mm
Calibration Group	H
DIN	863
Calibration Group Description	Internal micrometers (2 point)
Gross Weight	0.058 kg
Product Group	305

EAN

4059192005665