



### Signal Horn

- ideal for SCHABUS warning devices
- more discreet, smaller housing
- Simple installation in confined spaces
- designed for 230 V
- Loud acoustic warning tone

#### Einsatzgebiete:

- Small horn for acoustic applications
- 40 cm pre-assembled cables
- Housing made of impact-resistant ABS plastic
- Protection class IP54 (for vertical mounting)



Article number: 200892

The QR code will take you directly to the product page in our webshop

### Technical data

Operating voltage	230 V ~ A (±5%)/ 50 Hz	Protection class	IP54 for vertical mounting
Sound pressure	max. 100 dB (1m)	Functional area	-20° C / +50° C
Material	ABS plastic	Connection cable	UL1015/18 AWG (0,8 mm <sup>3</sup> )
Weight	0,11 kg	Article number	200982
Dimensions (HxWxD)	158 x Ø 75 mm, Hole spacing 44 mm	EAN:	4044764001046

### Signal horn

Signal horns in conjunction with our warning devices.  
For example, an acoustic signal can sound in the living area if a problem has occurred in the cellar.  
40 cm pre-assembled supply cable 2/3 x 0.75 mm<sup>2</sup> simplifies wiring.

Ideal in combination with SCHABUS top-hat rail warning devices that do not have a built-in acoustic alarm, e.g. SHT 5001 water detector, SHT 5002 level controller, GX-HS gas warning device.

The signalling horn is designed for indoor use and should therefore only be installed vertically; if installed outdoors, ensure that it is as dry and weather-protected as possible.