



NTE724 **Integrated Circuit** **Differential/Cascode Amplifier**

Description:

The NTE724 is a differential/cascode amplifier in an 8-Lead TO5 type metal can package designed for use in communications and industrial equipment operating at frequencies from dc to 120MHz.

Features:

- Controlled for Input Offset Voltage, Input Offset Current, and Input Bias Current
- Balanced Differential Amplifier Configuration with Controlled Constant-Current Source
- Single and Dual-Ended Operation

Applications:

- RF and IF Amplifiers (Differential or Cascode)
- DC, Audio, and Sense Amplifiers
- Converter in the Commercial FM Band
- Oscillator
- Mixer
- Limiter

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$ unless otherwise specified)

Power Dissipation ($T_A \leq +85^\circ\text{C}$), P_D	450mW
Derate Linearly Above 85°C	5mW/ $^\circ\text{C}$
Operating Ambient Temperature Range, T_{opr}	-55° to $+125^\circ\text{C}$
Storage Temperature Range, T_{stg}	-65° to $+150^\circ\text{C}$
Lead Temperature (During Soldering, 1/16" from case, 10sec max), T_L	$+265^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$, $V_{CC} = +12\text{V}$, $V_{EE} = -12\text{V}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Input Bias Current	I_{II}	$V_{CC} = +6\text{V}$, $V_{EE} = -6\text{V}$	—	16.6	70.0	μA
			—	36	106	μA
Quiescent Operating Current	I_6 or I_8	$V_{CC} = +6\text{V}$, $V_{EE} = -6\text{V}$	0.8	1.25	2.0	mA
			2.0	3.3	5.0	mA
AGC Bias Current (Into Constant Current Source Pin7)	I_7	$V_{CC} = 12\text{V}$, $V_{AGC} = 9\text{V}$	—	1.28	—	mA
		$V_{CC} = 12\text{V}$, $V_{AGC} = 12\text{V}$	—	1.65	—	mA

Electrical Characteristics (Cont'd): ($T_A = +25^\circ\text{C}$, $V_{CC} = +12\text{V}$, $V_{EE} = -12\text{V}$ unless otherwise specified)

Parameter	Symbol	Test Conditions		Min	Typ	Max	Unit
Input Current (Pin7)	I_7	$V_{CC} = +6\text{V}$, $V_{EE} = -6\text{V}$		0.5	0.85	1.0	mA
				1.0	1.65	2.1	mA
Device Dissipation	P_T	$V_{CC} = +6\text{V}$, $V_{EE} = -6\text{V}$		24	36	54	mW
				120	175	260	mW
Power Gain	G_P	$V_{CC} = 9\text{V}$, $f = 100\text{MHz}$	Cascode	16	20	—	dB
			Differential Amp	14	17	—	dB
		$V_{CC} = 9\text{V}$, $f = 10.7\text{MHz}$	Cascode	35	39	—	dB
			Differential Amp	28	32	—	dB
Noise Figure	NF	$V_{CC} = 9\text{V}$, $f = 100\text{MHz}$	Cascode	—	7.2	9.0	dB
			Differential Amp	—	6.7	9.0	dB
Power Output (Untuned)	P_o	$V_{CC} = 9\text{V}$, $f = 10.7\text{MHz}$	Diff. Amp 50Ω Input–Output	—	5.7	—	μW
AGC Range	AGC		Differential Amp	—	62	—	dB
Voltage Gain	A	$V_{CC} = 0\text{V}$, $f = 10.7\text{MHz}$ $R_L = 1\text{k}\Omega$	Cascode	—	40	—	dB
			Differential Amp	—	30	—	dB
Peak-to-Peak Output Current	I_{P-P}	$V_{CC} = 9\text{V}$	Differential Amp, $f = 10.7\text{MHz}$, $e_{in} = 400\text{mV}$	2.0	4.0	7.0	mA
		$V_{CC} = 12\text{V}$		3.5	6.0	10.0	mA

Pin Connection Diagram
(Top View)



