

ARTIKEL-NUMMER: 27-0513B  
**Honeywell CoreShield™-  
Handschuhe - 27-0513B**

CoreShield, 13-Gauge-Nylonträger, schwarz, Nitril-  
Mikroschaum-Beschichtung, schwarz, A7/F

**Honeywell**

## Überblick

**Artikelnummer**

27-0513B

**Produkttyp**

Handschuhe

**Produktlinie**

schnittfest

**Marke**

Honeywell

**Branche**

- Automobilindustrie und Bauteilproduktion
- Bauindustrie
- Glasindustrie
- Logistik
- Stahl- und Metallindustrie

## Eigenschaften und Nutzen

**Funktion**

CoreShield™-Spezialgarn

**Nutzen**

Einer der leichtesten Schnittschutzhandschuhe auf dem Markt, wirkt gegen Handermüdung bei Arbeitern, die den ganzen Tag lang Schutzhandschuhe tragen müssen. Hautfreundliche Garne, die gegen Allergien wirken und hervorragende Fingerbeweglichkeit ermöglichen

**Funktion**

CoreShield™-Mikroschaum-Nitril-Hochleistungsbeschichtung

**Nutzen**

Bietet durchgehende Atmungsaktivität, hervorragende Griffsicherheit, Abriebfestigkeit für doppelte Lebensdauer, Reduzierung der Handermüdung und hervorragende Fingerbeweglichkeit.

**Funktion**

Farbcodiertes Markierungssystem

**Nutzen**

Einfache Auswahl der richtigen Handschuhe für Ihre Anwendung

**Funktion**

Verstärkung am Daumen

**Nutzen**

Höhere Verschleißfestigkeit und längere Produktlebensdauer

**Funktion**

Waschbar

**Nutzen**

Geringere Betriebskosten

**Funktion**

Schutz von Hand und Handgelenk

**Nutzen**

Längeres Bündchen für besseren Schutz des Handgelenks

**Funktion**

Touchscreengeeignet – resistiv und kapazitiv

**Nutzen**

Zur Bedienung von Industriemaschinen- und Smartphone-Touchscreens, ohne die Handschuhe abzulegen

**Funktion**

Gauge 13

**Nutzen**

Hervorragende Passform und Fingerbeweglichkeit

**Technische Beschreibung**

**Beschreibung**

CoreShield, 13-Gauge-Nylonträger, schwarz, Nitril-Mikroschaum-Beschichtung, schwarz, A7/F

**Produkttechnologie**

CoreShield-Spezialgarn und Mikroschaum-Nitril-Hochleistungsbeschichtung

**Faser**

Polyester, Legierung, HPPE

**Strickstärke**

13

**Handschuh-/Trikotfarbe**

Schwarz

**Beschichtungstyp**

Nitril-Mikroschaum

**Beschichtungsfarbe**

Schwarz

**Länge**

255 mm Größe 9

**Größen**

6XS – 11XXL

**EN 388 - Mechanische Gefahren und Abriebfestigkeit**

Abriebfestigkeit	4
Schnittbeständigkeit (Coupe-Test)	X
Reißfestigkeit	4
Durchstichfestigkeit	4
Schnittbeständigkeit (TDM-Test)	F

**ASTM D3389-05**

ANSI-Level Abriebfestigkeit	6
-----------------------------	---

**ASTM F1790-97**

ANSI-Level Schnittbeständigkeit

A7

## Verpackungsetikett

**Maßeinheit**

Paar

## Drucksachen & Dokumentationen

CoreShield Micro foam Data Sheet UK

[http://www.honeywellsafety.com/supplementary/documents\\_and\\_downloads/secured/gloves/4295003580/1033.aspx](http://www.honeywellsafety.com/supplementary/documents_and_downloads/secured/gloves/4295003580/1033.aspx)

## Verpackung

**Maßeinheit**

PAA

**Menge pro Box/Packung/Versandkarton**

10

**Menge pro Karton**

100

**Mindestbestellmenge**

100

**Herkunftsland**

China

# CORESHIELD™ MICRO-FOAM NITRILE COATING

Having the right gloves for the right application is crucial to providing your workers with optimum protection.

Thanks to its high-performance fiber, the Honeywell CoreShield™ range of 22 styles offers complete cut protection from level A/A1 to F/A9, in a choice of 4 various gauges (from 10gg to 18gg) and 3 different coatings.

With CoreShield™, simplified hand protection is at your fingertips.

## INDUSTRIES

Manufacturing, Automotive, Metal stamping, Glass handling, Construction, Logistics

## APPLICATIONS

Please refer to CoreShield™ Selector Guide to choose your Honeywell CoreShield™ gloves

## FEATURES AND BENEFITS



### EASY TO CHOOSE

The color-coded marking system makes it easy for you to choose the gloves you need for your application, according to the new EN 388:2016 European standard and ANSI-105-2016 American standard. Choose by level of cut protection, grip, dexterity and fit.



### EASY TO WEAR

One of the lightest-weight cut-protective gloves on the market, they help to prevent hand fatigue for workers who need to wear them all day long.

Skin-friendly yarns that reduce the allergy risk to wearers. CoreShield™ gloves are certified STANDARD 100 by OEKO-TEX®.

Hand and wrist protection.

Touchscreen resistive and capacitive.



### COST-EFFECTIVE TO BUY

Thumb reinforcement.

CoreShield™ High Performance Coating has special abrasion technology for x2 durability coating.


The washability of the glove material means that even after 5 washing cycles, there are no significant changes in performance or size.

CoreShield™ gloves have a longer life, which in turn translates into less frequent replacements and reduced cost of ownership. Purchasing of CoreShield™ gloves is an investment.



CoreShield™   
Cut protection made simple

**Honeywell**



**CoreShield™ High Performance Micro-Foam Nitrile coating** provides 360° breathability, excellent grip performance, water and oil proof coating, abrasion resistance, reduced hand fatigue and excellent dexterity.

**CoreShield™ Engineered Yarn**  
Skin friendly and comfortable material to shield the cut resistant material  
Softer skin-friendly yarn in contact with the skin

## CORESHIELD™ CHOOSE YOUR MICRO-FOAM COATING

SKU	PRODUCT NAME & DESCRIPTION	CUT LEVEL & COLOR CODING	EN388:2016 PERFORMANCES	ANSI/ISEA 105:2016 PERFORMANCES		EN407 PERFORMANCES
				CUT	ABRASION	
21-1515B	CoreShield, 15 gauge nylon black liner, nitrile micro-foam black coating, A1/A	A1 A	4X31A	A1	6	
21-1518B	CoreShield, 18 gauge nylon black liner, nitrile micro-foam black coating, A1/A	A1 A	4X21A	A1	6	
22-7513B	CoreShield, 13 gauge HPPE black liner, nitrile micro-foam black coating, A2/B	A2 B	4X42B	A2	6	
22-7513W	CoreShield, 13 gauge HPPE white liner, nitrile micro-foam grey coating, A2/B	A2 B	4X42B	A2	6	
22-7518B	CoreShield, 18 gauge HPPE grey liner, nitrile micro-foam black coating, A2/B	A2 B	4X31B	A2	6	
23-0513B	CoreShield, 13 gauge HPPE/basalt black liner, nitrile micro-foam black coating, A3/C	A3 C	4X43C	A3	6	X1XXXX
23-7518B	CoreShield, 18 gauge HPPE/basalt black liner, nitrile micro-foam black coating A3/C	A3 C	4X42C	A3	6	X1XXXX
24-0513B	CoreShield, 13 gauge HPPE/basalt black liner, nitrile micro-foam black coating, A4/D	A4 D	4X43D	A4	6	
24-0513W	CoreShield, 13 gauge HPPE/basalt white liner, nitrile micro-foam grey coating, A4/D	A4 D	4X43D	A4	6	
24-9518B	CoreShield, 18 gauge, HPPE/steel black liner, nitrile micro-foam black coating, A4/D	A4 D	4X31D	A4	6	
25-0513B	CoreShield, 13 gauge HPPE/stainless steel black liner, nitrile micro-foam black coating, A5/E	A5 E	4X42E	A5	6	
26-0513W	CoreShield, 13 gauge HPPE/alloy/basalt white liner, nitrile micro-foam grey coating, A6/F	A6 F	4X44F	A6	6	
26-0513B	CoreShield, 13 gauge HPPE/alloy/basalt black liner, nitrile micro-foam black coating, A6/F	A6 F	4X44F	A6	6	
27-0513B	CoreShield, 13 gauge HPPE/alloy black liner, nitrile micro-foam coating, A7/F	A7 F	4X44F	A7	6	

### Washing instructions

- Maximum washing temperature 30°C/86°F mild process
- Do not bleach
- Tumble dry possible at low temperature, exhaust temperature max. 60°C/140°F
- Do not iron
- Do not dry clean

Packaging: Gloves are packed in a plastic bag by inner pack of 10 pairs, 10 inner packs per case (100 pairs).  
Sizes: from 6/XS to 11/XXL

### Honeywell Safety Products UK Limited

Edison Rd – Basingstoke RG21 6QD  
United Kingdom Phone: +44 (0) 1256 693 200  
info-uk.hsp@honeywell.com

### Honeywell Safety Products Europe SAS

Immeuble Edison Paris Nord 2  
33, rue des Vanesses – CS 55288 Villepinte  
95958 Roissy CDG Cedex – France  
+33 (0) 1 49 90 79 79  
info-export.hsp@honeywell.com

### Industrial Safety PPE Technical Support

Free Phone: 00 800 3344 2803 (free calls in Europe)  
Phone: +44 (0) 1698 647 087 (paid calls)  
IS.PPE.TECHSUPPORT.EUROPE@honeywell.com

[www.honeywellsafety.com](http://www.honeywellsafety.com)

HIS\_GLOVES\_CoreShield\_Micro-foam\_DTS\_ENa\_UK\_07/19  
© 2019 Honeywell International Inc.

**THE  
FUTURE  
IS  
WHAT  
WE  
MAKE IT**

**Honeywell**