




Thermocouple Extension & Compensating Cable

PVC Insulated & Screened



- PVC insulated & screened
- Twisted cores & screened construction for reduced electrical noise
- Conductors PVC insulated and twisted together, aluminium Mylar® tape screen & drain wire, overall PVC sheath
- General purpose cable both waterproof and flexible
- Thermocouple extension types for K, J
- Stranded 7/0.2mm conductors
- Available in 100 metre lengths
- Tolerance Class 2
- Insulation rating -10°C to 105°C
- Colour code (cores & jacket) to IEC-584-3

<u>Calibration Type</u>	<u>No. of Strands</u>	<u>Colour</u>	<u>Product Code</u>	<u>Manufacturer's Part Number</u>	<u>Rapid Part Number</u>
K	7/0.2 mm	 Type K	100M - K 7/0.2 PVC MYLAR IEC	XE-2112-100	61-3229
J	7/0.2 mm	 Type J	100M J 7/0.2 PVC MYLAR IEC	XE-2212-100	61-3230