

Product characteristics

Inductive sensor

Metal thread M30 x 1.5

Cable

Sensing range 10 mm; [f] flush mountable

Electrical data

Electrical design

DC NPN

Operating voltage [V]

15...30 DC

Current consumption [mA]

< 15

Protection class

III

Reverse polarity protection

yes

Outputs

Output function

normally open

Voltage drop [V]

< 2.5

Current rating [mA]

100

Short-circuit protection

pulsed

Overload protection

yes

Switching frequency [Hz]

200

Range

Sensing range [mm]

10

Real sensing range (Sr) [mm]

10 ± 10 %

Operating distance [mm]

0...8.1

Accuracy / deviations

Correction factors

mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.4 / Al approx. 0.4 / Cu approx. 0.3

Hysteresis [% of Sr]

1...20

Switch-point drift [% of Sr]

-10...10

Environment

Ambient temperature [°C]

-25...70

Protection

IP 67

Tests / approvals

EMC

EN 61000-4-2 ESD: 4 kV CD / 8 kV AD

EN 61000-4-3 HF radiated: 10 V/m

EN 61000-4-4 Burst: 2 kV

EN 61000-4-6 HF conducted: 3 V

EN 55011 (Emission): class B

MTTF [Years]

1268

Mechanical data

Mounting

flush mountable

Housing materials

housing: Brass nickel-plated; active face: PBT; lock nuts: Brass

Weight [kg]

0.18

Displays / operating elements

Output status indication

LED

yellow

II7106 - Inductive sensor - eclass: 27270101 / 27-27-01-01

Electrical connection

Connection

PVC cable / 2 m; 3 x 0.34 mm²; Ø 4.9 mm


Wiring

Core colours

BK black

BN brown

BU blue



Accessories

Accessories (included)

2 lock nuts

Remarks

Pack quantity

[piece]

1