

TWIN THERMOSTAT ZR011 0 TO +60 C



Model		
product brand name		SIVACON
Product designation		twin thermostat
General technical data		
Operating temperature / minimum	°C	-45
<b>Mechanical service life (switching cycles) / typical</b>		100 000
Voltage		
<b>Inrush current / typical</b>	A	10
Main circuit		
Operating voltage / Rated value	V	250
Product details		
<b>Product component</b>		
• digital display		No
• hygostat		No
Mechanical Design		
<b>Height</b>	mm	67
<b>Width</b>	mm	50
<b>Depth</b>	mm	46
<b>mounting position</b>		any
<b>Mounting type</b>		terminal mounting
Material / of the enclosure		plastic
Environmental conditions		
Relative humidity / Reference value	%	90

### Ambient temperature

• during storage / minimum	°C	-45
• during storage / maximum	°C	80

### Certificates

#### Equipment marking

• acc. to DIN EN 61346-2	K
• acc. to DIN EN 81346-2	K

### General Product Approval



### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21701EA>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21701EA/all>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR21701EA](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21701EA)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

11.03.2015