Connection Line M12 × 1; 4-pin



S23-10M


Part Number



Technical Data

Mechanical Data	
Connection 1	Socket, straight
Connection mode 1	M12 × 1, 4-pin
Connection 2	stripped
Torque	M12: 0,6 Nm
Cable Length	10 m
Cable Diameter	5 mm
Wire cross-section	0,34 mm ²
Degree of Protection	IP67
Temperature Range	-570 °C
Cable Jacket Material	PVC
Material Wire Insulation	PVC
Material Sleeve Nut	CuZn, nickel-plated
Packaging unit	1 Piece
Connection Diagram No.	S02
Connection Equipment No.	2

• Straight





Legen	d		F
+	Supply Voltage +		r
-	Supply Voltage 0 V		ι
~	Supply Voltage (AC Voltage)		Ū
А	Switching Output (NO	D)	١
Ā	Switching Output (NC	C)	١
V	Contamination/Error Output (NO	D)	(
V	Contamination/Error Output (NC	C)	¢
E	Input (analog or digital)		E
т	Teach Input		ł
Z	Time Delay (activation)		e
S	Shielding		Ł
RxD	Interface Receive Path		ę
TxD	Interface Send Path		S
RDY	Ready		E
GND	Ground		\$
CL	Clock		-
E/A	Output/Input programmable		0
0	IO-Link		F
PoE	Power over Ethernet		1
IN	Safety Input		E
OSSD	Safety Output		L
Signal	Signal Output		Þ
BI_D+/-	Ethernet Gigabit bidirect. data line	e (A-D)	F
ENORSAZ	Encoder 0-pulse 0-0 (TTL)		E

Groun Switch /- Ethern +/- Etherne Interfac Emittec Magnet Input contac EDM

Platinum measuring resistor	ENARS422	Encoder A/Ā (TTL)	
not connected	ENBRS422	Encoder B/B (TTL)	
Test Input	ENA	Encoder A	
Test Input inverted	ENв	Encoder B	
Trigger Input	AMIN	Digital output MIN	
Ground for the Trigger Input	Амах	Digital output MAX	
Analog Output	Аок	Digital output OK	
Ground for the Analog Output	SY In	Synchronization In	
Block Discharge	SY OUT	Synchronization OUT	
Valve Output	Out	Brightness output	
Valve Control Output +	м	Maintenance	
Valve Control Output 0 V	rsv	reserved	
Synchronization	Wire Colors according to DIN IEC 757		
Ground for the Synchronization	BK	Black	
Receiver-Line	BN	Brown	
Emitter-Line	RD	Red	
Grounding	OG	Orange	
Switching Distance Reduction	YE	Yellow	
 Ethernet Receive Path 	GN	Green	
 Ethernet Send Path 	BU	Blue	
Interfaces-Bus A(+)/B(-)	VT	Violet	
Emitted Light disengageable	GY	Grey	
Magnet activation	WH	White	
Input confirmation	PK	Pink	
Contactor Monitoring	GNYE	Green/Yellow	

System Components and Software