


CUBE20S ANALOG INPUT MODULE AI4

4X16BIT (I 0(4)...20 mA)

Expansion module

AI4 - (E) I

Current

[Link to Product](#)**Illustration**

Product may differ from Image

Approvals



Input

Conversion time (analog)	480 µs (all channels)
Resolution (analog)	15 Bit + sign
Accuracy	max. 0.3 %
Connection	Differential current input

Internal communication

Module Supply	via system connection
Current consumption	max. 60 mA from system, max. 20 mA externally (UI)

Technical Data

Operating voltage	24 V DC (20.4...28.8 V DC)
-------------------	----------------------------

General data

Protection	IP20
Connection	Spring clamp plug-in terminals: max. 1.5 mm ² (AWG 16)
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	0...+60 °C (storage temperature -25...+70 °C)
Dimensions H × W × D	109×12.9×76.5 mm

Current input signals

Load	max. 60 Ohm, (EN 61131-2)
Input range	0...20 mA, 4...20 mA

Diagnostic

Communication status	via LED
Diagnostic via LED	per module and channel
Diagnostic via BUS	per module
Monitoring - under voltage	yes
Monitoring - no voltage	no
Short circuit and overload	yes
Wire break upper/lower limit overload	per module via LED and BUS

Commercial data

country of origin	TH
customs tariff number	85389099
minimum order quantity	1