

XF201-3P IRT managed IE IRT Switch, 1x 10/100Mbit/s RJ45-Ports, 3x 100Mbit/s POF SC RJ Ports, bus adapter mount., fault signal contact with set- button, redundant power supply, PROFINET IO device, ,Network management, redundancy manager integrated incl. electron. manual on CD-ROM, C-plug optional



Transmission rate

Transfer rate	10 Mbit/s, 100 Mbit/s
---------------	-----------------------

Interfaces / for communication / integrated

Number of electrical connections	
<ul style="list-style-type: none"> for network components or terminal equipment 	1
number of 100 Mbit/s SC-RJ-ports / for POF FOC	
<ul style="list-style-type: none"> with push-pull connection system 	3

Interfaces / others

Number of electrical connections	
<ul style="list-style-type: none"> for signaling contact 	1
<ul style="list-style-type: none"> for power supply 	1
<ul style="list-style-type: none"> for redundant voltage supply 	1
Type of electrical connection	
<ul style="list-style-type: none"> for signaling contact 	2-pole terminal block
<ul style="list-style-type: none"> for power supply 	2-pole terminal block
design of the removable storage	
<ul style="list-style-type: none"> C-PLUG 	Yes

Signal-Inputs/outputs	
Operating voltage / of the signaling contacts	
<ul style="list-style-type: none"> at DC / Rated value 	24 V
Operating current / of the signaling contacts	
<ul style="list-style-type: none"> at DC / maximum 	0.1 A
Supply voltage, current consumption, power loss	
Type of voltage / of the supply voltage	DC
Supply voltage	
<ul style="list-style-type: none"> external 	24 V
<ul style="list-style-type: none"> external / minimum 	19.2 V
<ul style="list-style-type: none"> external / maximum 	28.8 V
Product component / fusing at power supply input	Yes
Consumed current / maximum	0.4 A
Power loss [W]	
<ul style="list-style-type: none"> at DC / at 24 V 	6 W
Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during operation 	0 ... 50 °C
<ul style="list-style-type: none"> during storage 	-40 ... +70 °C
<ul style="list-style-type: none"> during transport 	-40 ... +70 °C
Relative humidity	
<ul style="list-style-type: none"> at 25 °C / without condensation / during operation / maximum 	95 %
Protection class IP	IP20
Design, dimensions and weight	
Design	compact
Width	100 mm
Height	117 mm
Depth	74 mm
Net weight	0.25 kg
Mounting type	
<ul style="list-style-type: none"> 35 mm DIN rail mounting 	Yes
<ul style="list-style-type: none"> wall mounting 	No
<ul style="list-style-type: none"> S7-300 rail mounting 	No
<ul style="list-style-type: none"> S7-1500 rail mounting 	No
Product properties, functions, components / general	
Cascading in the case of a redundant ring / at reconfiguration time of ~ 0.3 s	50
Cascading in cases of star topology	any (depending only on signal propagation time)
Product functions / management, configuration	
Product function	

• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• Port mirroring	No
• multiport mirroring	No
• with IRT / PROFINET IO switch	Yes
• PROFINET IO diagnosis	Yes
• switch-managed	Yes

Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes

Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes
• Error statistics	Yes

Product functions / DHCP

Product function	
• DHCP client	Yes

Product functions / Redundancy

Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes

<ul style="list-style-type: none"> • high speed redundancy protocol (HRP) with standby redundancy 	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
<ul style="list-style-type: none"> • media redundancy protocol (MRP) with redundancy manager 	Yes
<ul style="list-style-type: none"> • Media Redundancy Protocol for Planned Duplication (MRPD) 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/operation in the PRP-network 	Yes
<ul style="list-style-type: none"> • Parallel Redundancy Protocol (PRP)/Redundant Network Access (RNA) 	No
<ul style="list-style-type: none"> • Passive listening 	Yes

Product functions / Security

Protocol / is supported	
<ul style="list-style-type: none"> • SSH 	Yes

Product functions / Time

Product function	
<ul style="list-style-type: none"> • SICLOCK support 	Yes
Protocol / is supported	
<ul style="list-style-type: none"> • NTP 	No
<ul style="list-style-type: none"> • SNTP 	Yes

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM 	FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4
<ul style="list-style-type: none"> • for hazardous zone 	EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X
<ul style="list-style-type: none"> • for safety / from CSA and UL 	UL 60950-1, CSA C22.2 No. 60950-1
<ul style="list-style-type: none"> • for hazardous zone / from CSA and UL 	ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4
<ul style="list-style-type: none"> • for emitted interference 	EN 61000-6-4 (Class A)
<ul style="list-style-type: none"> • for interference immunity 	EN 61000-6-2

Standards, specifications, approvals / CE

Certificate of suitability / CE marking	Yes
---	-----

Standards, specifications, approvals / miscellaneous

Certificate of suitability	EN 61000-6-2, EN 61000-6-4
<ul style="list-style-type: none"> • C-Tick 	Yes
<ul style="list-style-type: none"> • Railway application in accordance with EN 50155 	No

- Railway application in accordance with EN 50124-1
- KC approval

No

Yes

Accessories

Product extension / optional / C-PLUG

Yes

Further Information / Internet Links

Internet-Link

- to website: Selector SIMATIC NET SELECTION TOOL
- to website: Industrial communication
- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<http://www.siemens.com/snst>

<http://www.siemens.com/simatic-net>

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

Security information

Security information

Siemens provides products and solutions with industrial security functions that support the secure operation of plants, solutions, machines, equipment and/or networks. They are important components in a holistic industrial security concept. With this in mind, Siemens' products and solutions undergo continuous development. Siemens recommends strongly that you regularly check for product updates. For the secure operation of Siemens products and solutions, it is necessary to take suitable preventive action (e.g. cell protection concept) and integrate each component into a holistic, state-of-the-art industrial security concept. Third-party products that may be in use should also be considered. For more information about industrial security, visit <http://www.siemens.com/industrialsecurity>. To stay informed about product updates as they occur, sign up for a product-specific newsletter. For more information, visit <http://support.automation.siemens.com>. (V3.4)

last modified:

09/20/2017