

Twist drill, type N with insert 4xD

For universal use up to 1500 N/mm²

ORION[®]

Application:

Universal use in all material groups up to a strength of 1500 N/mm².

Execution:

- Twist drill with universal standard geometry and soldered cemented carbide insert (K20)

Advantage:

- Cemented carbide K20 insert ensures long service life
- polished chipping spaces ensure good chip removal
- cost-effective tool for broad range of applications



Art. no.	11163 240
Brand	ORION
Manufacturer Part Number	11163240
Cutting edge diameter	24 mm
Chip flute length	100 mm
Length	225 mm
DIN	8041
Gross Weight	0.561 kg
Product Group	140

EAN

4039247030538