

Hi-Power high-performance power chuck

In accordance with ISO 7388-1 (DIN 69871)

Application:

The high-performance power chuck combines high precision with high torque transmission and rigidity. Perfect for use in heavy machining during milling, but also for drilling and fine drilling operations.

Execution:

- High clamping force thanks to special slotted design and needle bearing.
- High rigidity for heavy machining
- High levels of precision and concentricity
- Axial length adjustment of 6 mm with stop screw

Advantage:

- Various applications when used with reduction sleeves ref. no. 23336450-455.
- Perfect for heavy machining.

Delivery:

1x high-performance power chuck in accordance with ISO 7388-1 (DIN 69871).



Art. no.	23297 201
Brand	BIG-DAISHOWA
Manufacturer Part Number	806754
Tool holding device	SK 40
Clamping diameter	20 mm
Projecting length	85 mm
Outer diameter	50 mm
Gross Weight	1.600 kg
Product Group	2AX