

## Electro-mechanical torque screwdriver

MANOSKOP 714 - display and release



### Execution:

- 4 measurement modes (torque, rotation angle, torque with control variable of rotation angle, rotation angle with control variable of torque)
- High-resolution colour graphic display with additional lateral signal lights, freely configurable menu structure
- 3 function modes: triggering, peak (displaying operation with peak value display) and track (displaying operation with current value display)
- Micro-USB 2.0 interface
- Data storage (2500 screwdriving processes), up to 200 screw joints in max. 25 processes can be programmed
- Measurement units: Nm, ft.lb, in.lb/automatically correct tightening torque on input of deviating actual dimension
- Feelable, optical and acoustic release signal, torque and angle of rotation visible simultaneously
- Automatic indication of the next calibration deadline depending on the time and/or the loading count
- Display resolution, rotation angle 0.1°
- Torque display resolution ≤ 60 Nm: 0.01 Nm > 60 Nm: 0.1 Nm



### Advantage:

- Quick and precise setting via keyboard, automatic key lock to protect against accidental changes to settings
- Overload protection by means of acoustic and optical warning signals and forced release (right)
- Reliable handling with ergonomically shaped handle (resistant to oils, greases, fuels, brake fluids and Skydrol)

### Delivery:

In robust plastic case (size 40 in sheet steel case), with software Sensomaster, USB cable, 4 micro batteries AAA/LR03, 1.5 V micro NiMH batteries AAA, 1.2 V can be used.

<b>Art. no.</b>	<b>52283 010</b>
<b>Brand</b>	STAHlwILLE
<b>Manufacturer Part Number</b>	96500910
<b>Min. torque</b>	10 Nm
<b>Max. torque</b>	100 Nm
<b>Min./max. torque</b>	10-100 Nm
<b>Insert shank square</b>	9 x 12 mm
<b>Length</b>	466 mm
<b>Error limit (%)</b>	2 %
<b>Gross Weight</b>	1.700 kg
<b>Product Group</b>	531

### EAN

4018754222827